



技术特性

温度范围: Temp. range $-65\sim+165^{\circ}\text{C}$ (PE Cable $-40\sim+85^{\circ}\text{C}$)
 振动: Vibration MTL-STD-202, Method 213
 特性阻抗: Impedance $50\ \Omega$
 频率范围: Frequency Range DC \sim 0-6GHz
 工作电压: Working Voltage 335V max (有效值)
 耐压: Withstand Voltage 1000V rms (海平面最小值)
 接触电阻: Contact resistance
 内导体之间: Center Contact $\leq 3\ \text{m}\Omega$
 外导体之间: Outer Contact $\leq 2\ \text{m}\Omega$
 绝缘电阻: Insulation resistance $\geq 5000\ \text{M}\Omega$
 插入损耗: Insertion loss $\leq 0.15\ \text{dB}/6\text{GHz}$

GENERAL TOLERANCE (UNLESS SPECIFIED) $\leq 10\ \pm 0.1$ $<10^{\circ}\leq 20\ \pm 0.2$ $<20^{\circ}\leq 50\ \pm 0.5$ Angle $\pm 3^{\circ}$	DWN		 连欣科技 Lian Xin Technology
	CHK		
 THIRD ANGLE	UNTT	REV	TITLE
	MM	A	STARF
SIZE	SHEET	PART NO	
A4	1 OF 1	SMA-KWE	
DRAWING NO			