

8-DIP

Description

# **KA3842AC/KA3842AE SMPS** Controller

## **Features**

FAIRCHILD SEMICONDUCTOR

- Low start current 0.2mA (Typ.)
- Operating range up to 500kHz
- Cycle by cycle current limiting
- Under Voltage Lock Out (UVLO) with hysteresis
- Short shutdown delay time: Typ.100ns
- High current totem-pole output
- Output swing limiting: 22V

## **Ordering Information**

Part Number	Operating Temp. Range	Pb-Free	Package	Packing Method
KA3842AC	-0 to +70°C	Yes	8-DIP	Tube
KA3842AE				



## **Absolute Maximum Ratings**

The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the Electrical Characteristics tables are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Symbol	Parameter	Value	Unit
V <sub>CC</sub>	Supply Voltage	30	V
Ι <sub>Ο</sub>	Output Current	±1	A
V <sub>I(ANA)</sub>	Analog Inputs (Pins 2, 3)	-0.3 to 6.3	V
I <sub>SINK(EA)</sub>	Error Amp. Output Sink Current	10	mA
PD	Power Dissipation	1	W
Rθja	Thermal Resistance, Junction-to-Air <sup>(4)</sup>	95	°C/W

### **Electrical Characteristics**

(V\_{CC} = 15V, R\_T = 10k<sup>3</sup>/<sub>4</sub>, C\_T = 3.3nF, T\_A = 0°C to +70°C, unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
REFEREN	CE SECTION	I				L
V <sub>REF</sub>	Output Voltage	$T_J = 25^{\circ}C, I_O = 1mA$	4.9	5.0	5.1	V
$\Delta V_{REF}$	Line Regulation	V <sub>CC</sub> = 12V to 25V	-	6	20	mV
	Load Regulation	I <sub>O</sub> = 1mA to 20mA	-	6	25	mV
I <sub>SC</sub>	Output Short Circuit	$T_A = 25^{\circ}C$	-	-100	-180	mA
OSILLATO	R SECTION	· · ·	•		•	•
F <sub>OSC</sub>	Initial Accuracy	$T_J = 25^{\circ}C$	47	52	57	kHz
STV	Voltage Stability	V <sub>CC</sub> = 12V to 25V	-	0.2	1	%
V <sub>OSC</sub>	Amplitude	V <sub>PIN4</sub> , Peak to Peak	-	1.7	-	V
I <sub>DISCHG</sub>	Discharge Current	$T_{\rm J} = 25^{\circ}{\rm C}$ , Pin 4 = 2V	7.8	8.3	8.8	mA
CURRENT	SENSE SECTION	· ·	•		•	•
G <sub>V</sub>	Gain <sup>(2)(3)</sup>		2.85	3	3.15	V/V
V <sub>I(MAX)</sub>	Maximum Input Signal <sup>(2)</sup>	V <sub>PIN1</sub> = 5V	0.9	1.0	1.1	V
PSRR	PSRR <sup>(1)(2)</sup>	$V_{CC} = 12V$ to 25V	-	70	-	dB
I <sub>BIAS</sub>	Input Bias Current		-	-2	-10	μA
T <sub>D</sub>	Delay to Output <sup>(1)</sup>	$V_{PIN3} = 0 V \text{ to } 2V$	-	100	200	ns
ERROR A	MPLIFIER SECTION					
VI	Input Voltage	T <sub>PIN1</sub> = 2.5V	2.42	2.50	2.58	V
I <sub>BIAS</sub>	Input Bias Current		-	-0.3	-2	μA
G <sub>VO</sub>	Open Loop Gain <sup>(1)</sup>	$V_0 = 2V$ to $4V$	65	90	-	dB
GBW	Unity Gain Bandwidth <sup>(1)</sup>	$T_J = 25^{\circ}C$	0.7	1	-	MHz
PSRR	PSRR <sup>(1)</sup>	V <sub>CC</sub> = 12V to 25V	60	70	-	dB
I <sub>SINK</sub>	Output Sink Current	V <sub>PIN2</sub> = 2.7V V <sub>PIN1</sub> = 1.1V	2	6	-	mA
ISOURCE	Output Source Current	V <sub>PIN2</sub> = 2.3V V <sub>PIN1</sub> = 5.0V	-0.5	-0.8	-	mA
V <sub>OH</sub>	Output High Voltage	V <sub>PIN2</sub> = 2.3V, R1 = 15k <sup>3</sup> / <sub>4</sub> to GND	5	6	-	V
V <sub>OL</sub>	Output Low Voltage	V <sub>PIN2</sub> = 2.7V R1 = 15k¾ to Pin 8	-	0.8	1.1	V

## Electrical Characteristics (Continued)

(V<sub>CC</sub> = 15V, R<sub>T</sub> = 10k<sup>3</sup>/<sub>4</sub>, C<sub>T</sub> = 3.3nF, T<sub>A</sub> = 0°C to +70°C, unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
OUTPUT S	ECTION				1	
V <sub>OL</sub>	Output Low Level	I <sub>SINK</sub> = 20mA	-	0.1	0.4	V
		I <sub>SINK</sub> = 200mA	-	1.5	2.2	V
V <sub>OH</sub>	Output High Level	I <sub>SOURCE</sub> = 20mA	13	13.5	-	V
		I <sub>SOURCE</sub> = 200mA	12	13.5	_	V
t <sub>R</sub>	Rise Time <sup>(1)</sup>	T <sub>J</sub> = 25°C, C1 = 1nF	-	40	100	ns
t <sub>F</sub>	Fall Time <sup>(1)</sup>	T <sub>J</sub> = 25°C, C1 = 1nF	-	40	100	ns
V <sub>OLIM</sub>	Output Voltage Swing Limit	V <sub>CC</sub> = 27V, C1 = 1nF	-	22	-	V
UNDER VO	DLTAGE LOCKOUT SECTION					
V <sub>TH</sub>	Start Threshold		15	16	17	V
V <sub>TL</sub>	Min. Operating Voltage (After turn on)		9	10	11	V
PWM SEC	TION			•		
D <sub>MAX</sub>	Maximum Duty Cycle		94	96	100	%
D <sub>MIN</sub>	Minimum Duty Cycle		-	-	0	%
TOTAL ST	ANDBY CURRENT			•		
I <sub>ST</sub>	Start-Up Current		-	0.2	0.4	mA
I <sub>CC</sub>	Operating Supply Current	$V_{PIN2} = V_{PIN3} = 0V$	-	11	17	mA
VZ	V <sub>CC</sub> Zener Voltage	I <sub>CC</sub> = 25mA	-	29	_	V

 $^{\ast}$  Adjust V\_{CC} above the start threshold before setting at 15V

Notes:

1. These parameters, although guaranteed, are not 100% tested in production.

2. Parameter measured at trip point of latch with V2 = 0V.

3. Gain defined as:  $G_V = \Delta V_{PIN1} \Delta V_{PIN3} (V_{PIN3} = 0 \text{ to } 0.8V)$ 

4. Junction-to-air thermal resistance test environments

#### PCB information:

Board thickness; 1.6mm, Board dimension: 76.2 X 114.3mm<sup>2</sup>, Ref.: EIA/JSED51-3 and EIA/JSED51-7 Board structure; Using the single layer PCB.



#### TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx <sup>™</sup>	FAST <sup>®</sup>	ISOPLANAR <sup>™</sup>	PowerSaver™	SuperSOT <sup>™</sup> -6
ActiveArray <sup>™</sup>	FASTr <sup>™</sup>	LittleFET <sup>™</sup>	PowerTrench <sup>®</sup>	SuperSOT <sup>™</sup> -8
Bottomless <sup>™</sup>	FPS <sup>™</sup>	MICROCOUPLER <sup>™</sup>	QFET <sup>®</sup>	SyncFET <sup>™</sup>
Build it Now <sup>™</sup>	FRFET <sup>™</sup>	MicroFET <sup>™</sup>	QS™	TCM <sup>™</sup>
CoolFET <sup>™</sup>	GlobalOptoisolator <sup>™</sup>	MicroPak <sup>™</sup>	QT Optoelectronics™	TinyLogic <sup>®</sup>
<i>CROSSVOLT</i> <sup>™</sup>	GTO <sup>™</sup>	MICROWIRE <sup>™</sup>	Quiet Series™	TINYOPTO <sup>™</sup>
DOME <sup>™</sup>	HiSeC <sup>™</sup>	MSX <sup>™</sup>	RapidConfigure™	TruTranslation <sup>™</sup>
EcoSPARK <sup>™</sup>	I <sup>2</sup> C <sup>™</sup>	MSXPro <sup>™</sup>	RapidConnect™	UHC <sup>™</sup>
E <sup>2</sup> CMOS <sup>™</sup>	<i>i-Lo</i> <sup>™</sup>	OCX <sup>™</sup>	µSerDes™	UltraFET <sup>®</sup>
EnSigna <sup>™</sup>	ImpliedDisconnect <sup>™</sup>	OCX <sup>™</sup>	ScalarPump™	UniFET <sup>™</sup>
EnSigna™	ImpliedDisconnect™	OCXPro™	ScalarPump <sup>™</sup>	UniFE1™
FACT™	IntelliMAX™	OPTOLOGIC®	SILENT SWITCHER <sup>®</sup>	VCX™
FACT Quiet Serie		OPTOPLANAR™	SMART START™	Wire™
Across the board The Power Fran Programmable A		PACMAN™ POP™ Power247™ PowerEdge™	SPM™ Stealth™ SuperFET™ SuperSOT™-3	

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

#### LIFE SUPPORT POLICY

FAIRCHILDÍS PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user. 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

#### **PRODUCT STATUS DEFINITIONS**

#### Definition of Terms

Product Status	Definition
Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.
	Formative or In Design First Production Full Production



BUY

Datasheet

datasheet

PDF

<u></u>=- '

Download this

Home >> Find products >>

**KA3842A** SMPS Controller

Contents

 General description Features

Qualification Support

- Product status/pricing/packaging
- •Order Samples

#### **General description**

The KA3842AC/KA3842AE are fixed PWM controller for Off Line and DC to DC converter applications. The internal circuits include UVLO, low start up current circuit, temperature compensated reference, high gain error amplifier, current sensing comparator, and high current totem pole output for driving a POWER MOSFET. Also KA3842AC/KA3842AE provides low start up current below 0.3mA and short shutdown delay time typ. 100ns. The KA3842AC/KA3842AE has UVLO threshold of 16V(on) and 10V(off). The KA3842AC/KA3842AE can operate within 100% duty cycle.

#### back to top

#### Features

- Low Start Current 0.2mA (Typ)
- Operating Range up to 500kHz
- Cycle by Cycle Current Limiting
- Under Voltage Lock Out With Hysteresis
- Short Shutdown Delay Time: Typ.100ns
- High Current Totem-Pole Output
- Output Swing Limiting: 22V

#### back to top

Product status/pricing/packaging BUY



#### **Related Links**

Request samples

How to order products

Product Change Notices (PCNs)

Support

Sales support

Quality and reliability

Design center

This page Print version

e-mail this datasheet

KA3842ACS	Full Production	Full Production	\$0.39	DIP	8	RAIL
KA3842AES	Full Production	Full Production	\$0.473	DIP	8	RAIL

\* Fairchild 1,000 piece Budgetary Pricing \*\* A sample button will appear if the part is available through Fairchild's on-line samples program. If there is no sample button, please contact a <u>Fairchild distributor</u> to obtain samples

Indicates product with Pb-free second-level interconnect. For more information click here.

#### back to top

(/

#### **Qualification Support**

Click on a product for detailed qualification data

Product
KA3842ACS
KA3842AES

#### back to top

#### © 2007 Fairchild Semiconductor



Products | Design Center | Support | Company News | Investors | My Fairchild | Contact Us | Site Index | Privacy Policy | Site Terms & Conditions | Standard Terms & Conditions (