



Test Procedure for the NCP333FCT2GEVB Evaluation Board

- 1. Set EN = GND
- 2. Connect 3.2 V between IN and GND
- 3. Check Vout = 0
- 4. Set EN = 2V
- 5. Check Vout = Vin
- 6. Set EN = GND
- 7. Check Vout decreases down to GND
- 8. Disconnect Vin