


ROHS



Typical Specifications
 1.Rating : DC 12V 50mA
 2.Contact Resistance: $\leq 50\text{m}\Omega$
 3.Insulation Resistance: $\geq 100\text{m}\Omega$
 4.Travel: $0.30\pm 0.1\text{mm}$
 5.Life : 100,000 Cycles
 6.Waterproof level: IP67

Circuit Diagram

NO.1		
PART NO	H	L
A	4.3	2.95
B	4.5	3.45
C	5.0	3.95
D	5.5	4.45
E	6.0	4.95
F	6.5	5.45
G	7.0	5.95
H	7.5	6.45
I	8.0	6.95
J	8.5	7.45
K	9.0	7.95
L	9.5	8.45
M	10.0	8.95

NO.2	
PART NO	vigor
3	160 ± 40
4	250 ± 40

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

(6)	Waterproof pad	—	1	silica gel	Black	_____
(5)	Cover	—	1	Brass	Tin Plated	_____
(4)	Keystoke	—	1	PPA	Black	_____
(3)	Contact	—	1	F.Ag/SUS	Plating silver	_____
(2)	Base	—	1	PPA	Black	_____
(1)	Terminal	—	2	Brass(0.3t)	Plating silver	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE
DRAWN	LIUCAN	2021.9.23
CHECKED		
APPROVALS		

HRD 鑫锐
ELECTRONICS CO.,LTD

TOLERANCES ARE		30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
10~30		± 0.20					
5~10		± 0.15					
~ 5		± 0.10		$\pm 2^\circ$			
DRAWING NO.							
SHEET 1 OF 1							

		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.
	A				