

MOSFET - Power, Single P-Channel, POWERTRENCH® -20 V, -11 A, 13 mΩ

FDMA008P20LZ

General Description

This device is designed specifically for battery charge or load switching in cellular handset and other ultraportable applications. It features a MOSFET with low on-state resistance and zener diode protection against ESD.

The WDFN6 (MicroFET 2.05x2.05) package offers exceptional thermal performance for its physical size and is well suited to linear mode applications.

Features

- Max $r_{DS(on)}$ = 13 mΩ at $V_{GS} = -4.5$ V, $I_D = -2.5$ A
- Max $r_{DS(on)}$ = 16 mΩ at $V_{GS} = -2.5$ V, $I_D = -1.4$ A
- Max $r_{DS(on)}$ = 20 mΩ at $V_{GS} = -1.8$ V, $I_D = -1.0$ A
- Max $r_{DS(on)}$ = 30 mΩ at $V_{GS} = -1.5$ V, $I_D = -0.85$ A
- Low Profile – 0.8 mm Maximum – in the New Package WDFN6 (MicroFET 2.05 × 2.05 mm)
- HBM ESD Protection Level > 1 kV Typical (Note 3)
- Free from Halogenated Compounds and Antimony Oxides
- RoHS Compliant

MOSFET MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter		Ratings	Unit
V _{DS}	Drain to Source Voltage		−20	V
V _{GS}	Gate to Source Voltage		±8	V
I _D	Drain Current	Continuous (Note 1a)	−11	A
		Pulsed (Note 5)	−164	
E _{AS}	Single Pulse Avalanche Energy (Note 4)		54	mJ
P _D	Power Dissipation	(Note 1a)	2.4	W
		(Note 1b)	0.9	
T _J , T _{STG}	Operating and Storage Junction Temperature Range		−55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



THERMAL CHARACTERISTICS

Symbol	Parameter		Ratings	Unit
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	52	°C/W
		(Note 1b)	145	




ON Semiconductor®

www.onsemi.com



WDFN6 2.05x2.05, 0.65P
CASE 483AV

MARKING DIAGRAM



&2 = Date Code
&K = Lot Code
&Z = Assembly Plant Code
008 = Specific Device Code

ORDERING INFORMATION

Device Marking	Device	Package	Shipping†
008	FDMA008P20LZ	WDFN6 (Pb-Free)	3000 Units/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

FDMA008P20LZ

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

OFF CHARACTERISTICS

BV _{DSS}	Drain to Source Breakdown Voltage	I _D = -250 μA, V _{GS} = 0 V	-20			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I _D = -250 μA, referenced to 25°C		-16		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -16 V, V _{GS} = 0 V			-1	μA
I _{GSS}	Gate to Source Leakage Current	V _{GS} = ±8 V, V _{DS} = 0 V			±1	μA

ON CHARACTERISTICS

V _{GS(th)}	Gate to Source Threshold Voltage	V _{GS} = V _{DS} , I _D = -250 μA	-0.4	-0.65	-1.4	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I _D = -250 μA, referenced to 25°C		3		mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = -4.5 V, I _D = -2.5 A		10	13	mΩ
		V _{GS} = -2.5 V, I _D = -1.4 A		12	16	
		V _{GS} = -1.8 V, I _D = -1.0 A		15	20	
		V _{GS} = -1.5 V, I _D = -0.85 A		20	30	
		V _{GS} = -4.5 V, I _D = -2.5 A, T _J = 125°C		12.8		
g _{FS}	Forward Transconductance	V _{DS} = -5 V, I _D = -2.5 A		26		S

DYNAMIC CHARACTERISTICS

C _{iss}	Input Capacitance	V _{DS} = -10 V, V _{GS} = 0 V, f = 1 MHz		3131	4383	pF
C _{oss}	Output Capacitance			424	594	
C _{rss}	Reverse Transfer Capacitance			386	540	
R _g	Gate Resistance			13	25	

SWITCHING CHARACTERISTICS

t _{d(on)}	Turn-On Delay Time	V _{DD} = -10 V, I _D = -2.5 A, V _{GS} = -4.5 V, R _{GEN} = 6 Ω		12	21	ns
t _r	Rise Time			17	30	
t _{d(off)}	Turn-Off Delay Time			239	382	
t _f	Fall Time			96	153	
Q _g	Total Gate Charge	V _{GS} = -4.5 V, V _{DD} = -10 V, I _D = -2.5 A		28	39	nC
Q _{gs}	Gate to Source Gate Charge			3.6		
Q _{gd}	Gate to Drain "Miller" Charge			6.2		

DRAIN-SOURCE DIODE CHARACTERISTICS


V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = -2 A (Note 2)		-0.6	-1.2	V
		V _{GS} = 0 V, I _S = -2.5 A (Note 2)		-0.8	-1.3	V
t _{rr}	Reverse Recovery Time	I _F = -6.8 A, di/dt = 100 A/μS		28	46	ns
Q _{rr}	Reverse Recovery Charge			10	17	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. R_{θJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.



a. 52 °C/W when mounted on a 1 in² pad of 2 oz copper



b. 145 °C/W when mounted on a minimum pad of 2 oz copper

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.
3. The diode connected between the gate and the source serves only as protection against ESD. No gate overvoltage rating is implied.
4. E_{AS} of 54 mJ is based on starting T_J = 25°C, L = 3 mH, I_{AS} = 6 A, V_{DD} = 20 V, V_{GS} = 4.5 V. 100% test at L = 0.1 mH, I_{AS} = 19 A.
5. Pulsed Id please refer to Figure 10. SOA curve for more details.


TYPICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current


TYPICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Forward Bias Safe Operating Area




Figure 11. Single Pulse Maximum Power Dissipation



TYPICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

Figure 12. Junction-to-Ambient Transient Thermal Response Curve

ON



DATE 02 APR 2019






Figure 1 is a detailed cross-sectional diagram of a multi-layered composite structure. The diagram shows a central vertical core (1) with a cross-hatched pattern, flanked by two side layers (2 and 3). The top layer (4) is a thin, solid layer. The bottom layer (5) is a thick, solid layer. The diagram is divided into three main sections: a top section (6), a middle section (7), and a bottom section (8). Dimensions are given in inches. The total height is 1.825 inches. The total width is 1.300 inches. The top section (6) has a height of 0.250 inches. The middle section (7) has a height of 1.050 inches. The bottom section (8) has a height of 0.475 inches. The side layers (2 and 3) have a thickness of 0.370 inches. The top layer (4) has a thickness of 0.040 inches. The bottom layer (5) has a thickness of 0.660 inches. The central core (1) has a width of 0.650 inches. The side layers (2 and 3) have a width of 0.345 inches. The top layer (4) has a width of 0.400 inches. The bottom layer (5) has a width of 0.400 inches. The diagram is labeled with various dimensions and section numbers.

1. CONTROLLING DIMENSION: MILLIMETERS.
2. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
4. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.60	0.70	0.80
A1	0.00	-	0.05
A4	(0.20)		
b	0.25	0.30	0.35
D	1.95	2.05	2.15
D2	0.84	0.89	0.94
D3	(0.95)		
E	1.95	2.05	2.15
E2	1.45	1.50	1.55
e	0.65 BSC		
e1	1.30 BSC		
k	(0.35)		
k1	(0.45)		
L	0.18	0.28	0.38
L3	0.25	0.30	0.35
L4	0.55	0.60	0.65
L5	(0.23)		
aaa	0.10		
bbb	0.10		
ccc	0.05		
ddd	0.05		
eee	0.05		

DOCUMENT NUMBER:	98AON13671G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	WDFN6 2.05X2.05, 0.65P	PAGE 1 OF 1

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales