


### Features

- $V_{DS} = 200V$
- $I_D = 1.5A$
- $R_{DS(ON)} \leq 0.7\Omega @ V_{GS} = 10V$

### Application

- Load/Power Switching
- Interfacing Switching
- Battery Management for Ultra Small Portable Electronics
- Logic Level Shift

### Package and Pin Configuration



### Marking:262P

### Absolute Maximum Ratings ( $T_A=25^\circ C$ unless otherwise noted)

| Characteristics                        | Symbol         | Rating   | Unit       |
|--|----------------|----------|------------|
| Drain-Source Voltage                   | $V_{DSS}$      | 200      | V          |
| Gate-Source Voltage                    | $V_{GSS}$      | $\pm 20$ | V          |
| Continuous Drain Current               | $I_D$          | 1.5      | A          |
| Pulsed Drain Current <sup>(1)</sup>    | $I_{DM}$       | 4.5      | A          |
| Power Dissipation                      | $P_d$          | 1.6      | W          |
| Junction and Storage Temperature Range | $T_J, T_{stg}$ | -55~150  | $^\circ C$ |

### Thermal Characteristics


| Characteristics  | Symbol          | Rating | Unit         |
|--|-----------------|--------|--------------|
| Thermal Resistance, Junction-to-Ambient <sup>(1)</sup> | $R_{\theta JA}$ | 90     | $^\circ C/W$ |
| Thermal Resistance, Junction-to-Case <sup>(1)</sup>    | $R_{\theta JC}$ | 30     |              |

**Electrical Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise noted)**

| Characteristics  | Symbol       | Test Condition  | Min | Typ  | Max | Unit          |
|--|--------------|---|-----|------|-----|---------------|
| <b>Static Characteristics</b>                            |              |   |     |      |     |               |
| Drain-Source Breakdown Voltage                           | $BV_{DSS}$   | $I_D = 250\mu\text{A}, V_{GS} = 0\text{V}$                                      | 200 | -    | -   | V             |
| Gate Threshold Voltage                                   | $V_{GS(th)}$ | $V_{DS} = V_{GS}, I_D = 250\mu\text{A}$   | 2.0 | 3.0  | 4.0 |               |
| Drain Cut-Off Current                                    | $I_{DSS}$    | $V_{DS} = 160\text{V}, V_{GS} = 0\text{V}$                                      | -   | -    | 1   | $\mu\text{A}$ |
| Gate Leakage Current                                     | $I_{GSS}$    | $V_{GS} = \pm 20\text{V}, V_{DS} = 0\text{V}$                                   | -   | -    | 100 | nA            |
| Drain-Source ON Resistance                               | $R_{DS(on)}$ | $V_{GS} = 10\text{V}, I_D = 1.0\text{A}$  | -   | 0.55 | 0.7 | $\Omega$      |
| Forward Transconductance                                 | $g_{fs}$     | $V_{DS} = 10\text{V}, I_D = 1.0\text{A}$  | -   | 4.0  | -   | S             |
| <b>Dynamic Characteristics</b>                           |              |   |     |      |     |               |
| Total Gate Charge  | $Q_g$        | $V_{DS} = 100\text{V}, V_{GS} = 10\text{V}, I_D = 1.0\text{A}$                  | -   | 5.1  | -   | nC            |
| Gate-Source Charge                                       | $Q_{gs}$     |   | -   | 1.5  | -   |               |
| Gate-Drain Charge  | $Q_{gd}$     |   | -   | 2.0  | -   |               |
| Input Capacitance  | $C_{iss}$    | $V_{DS} = 100\text{V}, V_{GS} = 0\text{V}, f = 1\text{MHz}$                     | -   | 220  | -   | pF            |
| Reverse Transfer Capacitance                             | $C_{rss}$    |   | -   | 5.6  | -   |               |
| Output Capacitance                                       | $C_{oss}$    |   | -   | 46.9 | -   |               |
| Turn-On Delay Time                                       | $t_{d(on)}$  | $V_{DD} = 100\text{V}, I_D = 1\text{A}, V_{GS} = 10\text{V}, R_{GEN} = 6\Omega$ | -   | 6.3  | -   | ns            |
| Rise Time  | $t_r$        |   | -   | 6.3  | -   |               |
| Turn-Off Delay Time                                      | $t_{d(off)}$ |   | -   | 19.5 | -   |               |
| Fall Time  | $t_f$        |   | -   | 10.7 | -   |               |
| <b>Drain-Source Body Diode Characteristics</b>           |              |   |     |      |     |               |
| Maximum Continuous Drain to Source Diode Forward Current | $I_S$        |   | -   | 1.5  | -   | A             |
| Source-Drain Diode Forward Voltage                       | $V_{SD}$     | $I_S = 1.5\text{A}, V_{GS} = 0\text{V}$   | -   | -    | 1.4 | V             |
| Body Diode Reverse Recovery Time                         | $t_{rr}$     | $I_F = 1.3\text{A}, di/dt = 100\text{A}/\mu\text{s}$                            | -   | 81   | -   | ns            |
| Body Diode Reverse Recovery Charge                       | $Q_{rr}$     |   | -   | 0.25 | -   | $\mu\text{C}$ |



SOT23-6 Package Information



| Symbol | Dimensions In Millimeters |       | Dimensions In Inches |       |
|--------|---------------------------|-------|----------------------|-------|
|        | Min                       | Max   | Min                  | Max   |
| A      | 1.050                     | 1.250 | 0.041                | 0.049 |
| A1     | 0.000                     | 0.100 | 0.000                | 0.004 |
| A2     | 1.050                     | 1.150 | 0.041                | 0.045 |
| b      | 0.300                     | 0.500 | 0.012                | 0.020 |
| c      | 0.100                     | 0.200 | 0.004                | 0.008 |
| D      | 2.820                     | 3.020 | 0.111                | 0.119 |
| E      | 1.500                     | 1.700 | 0.059                | 0.067 |
| E1     | 2.650                     | 2.950 | 0.104                | 0.116 |
| e      | 0.950(BSC)                |       | 0.037(BSC)           |       |
| e1     | 1.800                     | 2.000 | 0.071                | 0.079 |
| L      | 0.300                     | 0.600 | 0.012                | 0.024 |
| θ      | 0°                        | 8°    | 0°                   | 8°    |