


1.Feature:

- ◆ Compliant with IEEE 802.3 standard
- ◆ Comply with RoHS & Halogen Free requirements.
- ◆ Operating Temperature:-40°C~+85°C
- ◆ Storage temperature range:-25°C to + 120°C.


Electrical Specification @25°C

Inductance:	350 uH Min. @ 100 KHz, 100mV 8mA DC Bias			
Hi-POT :	1500Vrms 1mA 1Second			
Turn Ratio:	1CT:1CT±3%			
Cw/w:	35pF Max			
Insertion Loss:	-1dB Max. @1MHz ~100MHz			
RETURN LOSS(RL) (Z out=100 OHM)	1-40MHz	50 MHz	6-80MHz	100MHz
	-18dB Min.	-14dB Min.	-12dB Min.	-10MHz
Cross Talk:	1MHz-100MHz			
	-30dBMin.			
CMRR	1MHz-100MHz			
	-30dBMin.			

2.Schematic:




3.Mechanical:



Units:mm[Inches] Tolerances:xx. x0±0.25[0.010] 0. xx±0.05[0.002]

4. Recommend reflow soldering curve:

Lead-free Recommended Soldering Profile:
(SMD parts)



Remarks:

- peak temperature (Tp) = See temperature classification
- Maximum preheat rate = 3°C/sec
- Ramp up rate = 3°C/sec Max
- Time above 217°C = 60 sec Min / 150 sec Max
- Maximum cooling rate = 6°C/sec
- T25°C to peak = 8 min Max
- preheat Time = 60 ~ 120 sec
- The number of allowed cycles in IR reflow ≤ 2 cycles

Standard Packing Quantity 800 pcs / reel