



Circuit Diagram PCB Layout(Pattern side)

NO.1			
PART NO	H	PART NO	H
A	4.3	O	11
B	4.5	P	11.5
C	5	Q	12
D	5.5	R	12.5
E	6	S	13
F	6.5	T	13.5
G	7	U	14
H	7.5	V	14.5
I	8	W	15
J	8.5	X	15.5
K	9	Y	16
L	9.5	Z	16.5
M	10		17
N	10.5		17.5

NO.2		
PART NO	vigor	
070	70±30	
100	100±50	
160	160±50	
250	250±50	
320	320±80	
350	350±80	
520	520±130	

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑦	Gasket	1	Nylon	
⑥	Waterproof Silicone	1	Silica gel	
⑤	Terminal	4	Brass(0.3t)	Plating silver
④	Contact	1	F-Ag/CS210	
③	Base	1	Nylon	Black
②	Cover	1	Nylon	
①	Keystoke	1	Nylon	Black

APPROVALS		DATE	DRAWING NO.	
DRAWN		G.M.Chen	2015/6/10	TC-1812SR-XXH-XXX
CHECKED				TACT SWITCHES
APPROVALS				PART NO.
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE
		10 ^{±0.10}	±0.20	UNIT: mm
		5 ^{±0.10}	±0.15	SCALE: 1:1
ECN NO.	REV.	DATE.	DESCRIPTION.	PROJ.
	A		NEW	

