




SOT-89 Plastic-Encapsulate Voltage Regulators

78L12

Three-terminal positive voltage regulator

Features:

Maximum Output current I_o : 0.1A
 Output voltage V_o : 12V
 Continuous total dissipation
 P_D : 0.6W ($T_a = 25^\circ\text{C}$)



Marking: 78L12

Absolute Maximum Ratings (Operating temperature range applies unless otherwise specified)


Symbol	Parameter		Value	Unit
V_i	Input Voltage		30	V
T_{OPR}	Operating Junction Temperature Range		-25 to +150	°C
T_{STG}	Storage Temperature Range		-55 to +150	°C

Electrical Characteristics at Specified Virtual Junction Temperature

($V_i=19\text{V}$, $I_o=40\text{mA}$, $C_i=0.33\mu\text{F}$, $C_o=0.1\mu\text{F}$, unless otherwise specified)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
V_o	Output Voltage	25°C	11.5	12	12.5	V
		14V≤ V_i ≤27V, I_o =1mA-40mA	11.4	12	12.6	V
		I_o =1mA-70mA	11.4	12	12.6	V
ΔV_o	Load Regulation	I_o =1mA-100mA	25°C	22	100	mV
		I_o =1mA - 40mA	25°C	13	50	mV
ΔV_o	Line Regulation	14V≤ V_i ≤27V	25°C	55	250	mV
		16V≤ V_i ≤27V	25°C	49	200	mV
I_q	Quiescent Current	25°C		4.3	6.5	mA
ΔI_q	Quiescent Current Change	16V≤ V_i ≤27V	0-125°C		1.5	mA
		1mA≤ I_o ≤40mA	0-125°C		0.1	mA
V_N	Output Noise Voltage	$f = 10\text{Hz}$ to 100KHz	25°C	70		µV
RR	Ripple Rejection	$f = 120\text{Hz}$, $15\text{V} \leq V_i \leq 25\text{V}$	0-125°C	37	42	dB
V_d	Dropout Voltage		25°C		1.7	V

Typical Application



Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.

Typical Characteristics

