


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

1. ELECTRICAL:

- 1.1. VOLTAGE RATING:DC 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.


2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:2.5* 15 mm 套管	1
②	接头	SMA 公头直头,公针,镀金	1
①	同轴线	RG1.37黑色同轴线, OD:1.37mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO.,LTD.

ALL DIMENSION ARE IN MM	DRI	DATE	KH-SMAJ-221-RG1.37-B200
	DRAIN. Jamy	2023/8/11	
COMPUTER GENERATED IN SOLIDWORKS	CHK. Alan	2023/8/11	
DO NOT SCALE THIS DRAWING	APP. Ellis	2023/8/11	
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		www.kinghelm.com.cn 0755-28190160
SCALE: Free		TYPE	SHEET 1 OF 1