








RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

SPECIFICATION:


1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



深圳市连欣科技有限公司

DESCRIPTION		USB C F TYPE DIP+SMT CONN					
DRAWING NO		170817-004		PART NO.		XUBF-0336-B07	
THIRD ANGLE PROJECTION 	REVISION	A	UNIT	MM	DRAWN	Charles	
	LINEAR X. ±0.50 X. ±5* X.X ±0.38 X.X ±2* X.XX ±0.25 X.XX ±1*	ANGLE	SCALE	N/A	CHECKED		
			SHEET	1/1	APPROVED		