# $\begin{tabular}{l} $$TIB82S105BC$ 16 $\times$ 48 $\times$ 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER$ WITH 3-STATE OUTPUTS OR PRESET\end{tabular}$

- 50-MHz Clock Rate
- Power-On Preset of All Flip-Flops
- 6-Bit Internal State Register With 8-Bit Output Register
- Power Dissipation . . . 600 mW Typical
- Programmable Asynchronous Preset or Output Control
- Functionally Equivalent to, but Faster Than 82S105A<sup>†</sup>

#### description

The TIB82S105BC is a TTL field-programmable state machine of the Mealy type. This state machine (logic sequencer) contains 48 product terms (AND terms) and 14 pairs of sum terms (OR terms). The product and sum terms are used to control the 6-bit internal state register and the 8-bit output register.

The outputs of the internal state register (P0–P5) are fed back and combined with the 16 inputs (I0–I15) to form the AND array. In addition a single sum term is complemented and fed back to the AND array, which allows any of the product terms to be summed, complemented, and used r s an input to the AND array.

The state and output registers are positi re-ec getriggered S/R flip-flops. These registers are unconditionally preset high during owner up. Pin19 can be used to preset both rrugisters or, by blowing the proper fuse, be converted to an output control function.

The TIB82S105BC is characterized for operation from 0°C to 75°C.



† Power-up preset and asynchronous preset functions are not identical to 82S105A. See Recommended Operating Conditions.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright  $\ensuremath{\textcircled{}}$  1995, Texas Instruments Incorporated

## TIB82S105BC 16 × 48 × 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET SRPS025A – D2897, SEPTEMBER 1985 – REVISED NOVEMBER 1995

SRPS025A – D2897, SEPTEMBER 1985 – REVISED NOVEMBER 1

# functional block diagram (positive logic)





# TIB82S105BC 16 $\times$ 48 $\times$ 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995

#### logic diagram (positive logic)



NOTES: 1. All AND gate inputs with a blown link float to the high level.

2. All CR years inputs with a blown link float to the low level.

3. Fuse ... mbers = First fuse number + Increment



# **TIB82S105BC** $16 \times 48 \times 8$ FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995

## absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, V <sub>CC</sub> (see Note 4) 7 V Input voltage (see Note 4) 5.5 V
Voltage applied to disabled output (see Note 4) 5.5 V
Operating free-air temperature range
Storage temperature range65°C to 150°C

NOTE 4: These ratings apply except for programming pins during a programming cycle.

#### recommended operating conditions

			MIN	NOM	MAX	UNIT	
VCC	Supply voltage		4.75	5	5.25	V	
VIH	High-level input voltage		2		5.5	V	
VIL	Low-level input voltage	0			0.8	V	
ЮН	High-level output current				-3.2	mA	
IOL	Low-level output current				24	mA	
fclock	Clock frequency <sup>†</sup>	1 thru 48 product term whilout C-array ‡	0		50	MHz	
		1 thru 48 product cruss with C-array	0		30		
+	Pluse duration	Clock high or low	10			ns	
tw		Preset	15			113	
+	Setup time before CLK↑,	Without C-array	15			ns	
t <sub>su</sub>	1 thru 48 product terms	With C-ar ay	30				
t <sub>su</sub>	Setup time, Preset low (inactive) before CLK <sup>\$</sup>		8			ns	
t <sub>h</sub>	Hold time, input after CLK↑		0			ns	
Тд	Operating free-air temperature		0	25	75	°C	

<sup>†</sup>The maximum clock frequency is independent of the internal programmed configuration. If an output is fed back externally to an input, the maximum clock frequency must be calculated.

<sup>‡</sup> The C-array is the single sum term that is complemented and educate to the AND array. , resum.

§ After Preset goes inactive, normal clocking resumes on the first low-to-high clock transition.

INSTRUMENTS POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

# TIB82S105BC 16 $\times$ 48 $\times$ 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS		MnN	ı YP†	MAX	UNIT
VIK	V <sub>CC</sub> = 4.75 V,	lj = -18 mA				-1.2	V
VOH	V <sub>CC</sub> = 4.75 V,	$I_{OH} = -3.2 \text{ mA}$	(	. 4	3		V
V <sub>OL</sub>	V <sub>CC</sub> = 4.75 V,	I <sub>OL</sub> = 24 mA			0.37	0.5	V
IOZH	V <sub>CC</sub> = 5.25 V,	$V_{O} = 2.7 V$	Co			20	μA
IOZL	V <sub>CC</sub> = 5.25 V,	$V_{O} = 0.4 V$				-20	μA
lj	V <sub>CC</sub> = 5.25 V,	V <sub>I</sub> = 5.5 V				25	μA
IIH	V <sub>CC</sub> = 5.25 V,	V <sub>I</sub> = 2.7 V				20	μA
IIL	V <sub>CC</sub> = 5.25 V,	V <sub>I</sub> = 0.4 V				-0.25	mA
IO‡	V <sub>CC</sub> = 5.25 V,	V <sub>O</sub> = 2.25 V		-30		-112	mA
ICC	V <sub>CC</sub> <u>= 5</u> .25 V, PRE/OE at GND,	VI = 4.7 V, Outputs open	Z		120	180	mA

# switching characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITION	MIN	түр†	MAX	UNIT
	Without	C array		50	70		
f <sub>max</sub> §	With C	array		30	45		MHz
<sup>t</sup> pd	CLK↑	Q	R1 = 500 Ω,		8	15	ns
<sup>t</sup> pd	PRE↑	Q	R2 = 500 Ω,		12	20	ns
<sup>t</sup> pd	V <sub>CC</sub> ↑	0	See Figure 5		0	10	ns
t <sub>en</sub>	OE↓	2			10	20	ns
<sup>t</sup> dis	OE↑	Q			5	10	ns

<sup>†</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

<sup>‡</sup> The output conditions hace been chosen to produce a current that closely approximates one half of the true short-circuit output current, I<sub>OS</sub>. § f<sub>max</sub> is independent of the internal programmed configuration, and the number of product terms used.

#### programming information

Texas Instruments Programmable Logic Devices can be programmed using widely available software and inexpensive device programmers.

Complete programming specifications, algorithms, and the latest information on hardware, software, and firmware are available upon sequest. Information on programmers capable of programming Texas Instruments Programmable Logic is also evailable, upon request, from the nearest TI field sales office, local authorized TI distributor, or by calling Texas Instruments at (214) 997-5666.



## TIB82S105BC 16 × 48 × 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET SRPS025A – D2897, SEPTEMBER 1985 – REVISED NOVEMBER 1995

#### diagnostics

A diagnostics mode is provided with these devices that allows the user to inspect the contents of the state register. When I0 (pin 9) is held at 10 V, the state register bits P0–P5 will appear at  $m_2$  Q0–Q5 outputs and Q6–Q7 will be high. The contents of the output register will remain unchanged.





# TIB82S105BC $16 \times 48 \times 8$ FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995

#### test array

A test array that consists of product lines 48 and 49 has been added to these devices to a low testing prior to programming. The test array is factory programmed as shown in Table 1. Testing is accomplished by connecting Q0–Q7 to I8–I15, PRE/OE to GND, and applying the proper input signals as shown in Figure 2. Product lines 48 and 49 must be deleted during user programming to avoid interference with the rangrammed logic function.





### TIB82S105BC 16 × 48 × 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET SRPS025A – D2897, SEPTEMBER 1985 – REVISED NOVEMBER 1995

### TIB82S105B, 82S105A COMPARISON

The Texas Instruments TIB82S105B is a  $16 \times 48 \times 8$  Field-Programmable Logic Sequencer that is functionally equivalent to the Signetics 82S105A. However, the TIB82S105B is designed for a maximum speed of 50 MHz with the preset function being made conventional. As a result the TIB82S105B differs from the 22S105A in speed and in the preset recovery function.

The TIB82S105B is a high-speed version of the original 82S105A. The TIB82S105L features increased switching speeds with no increase in power. The maximum operating frequency is increased from 20 MHz to 50 MHz and does not decrease as more product terms are connected to each sum (OR) line. For instance, if all 48 product terms were connected to a sum line on the original 82S105A, the  $f_{max}$  would be about 15 VHz. The  $f_{max}$  for the TIB82S105B remains at 50 MHz regardless of the programmed configuration. In addition, the preset recovery sequence was changed to a conventional recovery sequence, providing quicker clock recovery times. This is explained in the following paragraph.

The TIB82S105B and the 82S105A are equipped with power-up preset and asynchronous preset functions. The power-up preset causes the registers to go high during power up. The asynchronous preset inhibits clocking and causes the registers to go high whenever the preset pin is taken hig! //fter a power-up preset occurs, the minimum setup time from power up to the first clock pulse must be met in order to assure that clocking is not inhibited. In a similar manner after an asynchronous preset, the preset input must return to unactive) for a given time, t<sub>su</sub>, before clocking.

The Signetics 82S105A was designed in such a way that after both power-up preset and asynchronous preset it requires that a high-to-low clock transition occur before a clocking transition (low-to-high) will be recognized. This is shown in Figure 3. The Texas Instruments TIB82S105B doe and require a high-to-low clock transition before clocking can be resumed, it only requires that the preset be inactive 8 ns (preset inactive-state setup time) before the clock rising edge. See Figure 4.

The TIB82S105B, with an f<sub>max</sub> of 50 MHz, is ideal for systems in which the state machine must run several times faster than the system clock. It is recommended that the TIP 32S105B be used in new designs. *However, if the TIB82S105B is used to replace the 82S105A, then the customer nust understand that clocking will begin with the first clock rising edge after preset.* 

PARAMETER	82S105A SIGNETICS	TIB82S105B TI ONLY		
ч, эх	20 MHz	50 MHz		
tpd, CLi Li Q	20 ns	15 ns		
K C C C C C C C C C C C C C C C C C C C				

## Table 3. Speed Differences



# TIB82S105BC $16 \times 48 \times 8$ FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995





# TIB82S105BC 16 $\times$ 48 $\times$ 8 FIELD-PROGRAMMABLE LOGIC SEQUENCER WITH 3-STATE OUTPUTS OR PRESET

SRPS025A - D2897, SEPTEMBER 1985 - REVISED NOVEMBER 1995



NOTES: A. CL includes probe and its capacitance and is 50 pF for tpd and ten, 5 pF for tdis.

- B. All input pulses have the following characteristics:  $PRR \le 1$  MHz,  $t_f = t_f = 2$  ns, duty cycle = 50%.
- C. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- D. When measuring, ropagation delay times of 3-state outputs, switch S1 is closed.
- E. Equivalent 'bads may be used for testing.





# PACKAGING INFORMATION

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
TIB82S105BCFN	OBSOLETE	PLCC	FN	28	TBD	Call TI	Call TI
TIB82S105BCN	OBSOLETE	PDIP	Ν	28	TBD	Call TI	Call TI

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details. TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **MECHANICAL DATA**

MPDI008 - OCTOBER 1994

#### N (R-PDIP-T\*\*)

#### PLASTIC DUAL-IN-LINE PACKAGE

24 PIN SHOWN



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MS-011
- D. Falls within JEDEC MS-015 (32 pin only)



# **MECHANICAL DATA**

MPLC004A - OCTOBER 1994

#### PLASTIC J-LEADED CHIP CARRIER

# FN (S-PQCC-J\*\*)



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

C. Falls within JEDEC MS-018



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address:

Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2005, Texas Instruments Incorporated