


3.2 × 2.5 mm SMD Crystal Oscillator

Feature

- Typical 3.2 x 2.5 x 0.95mm SMD package.
- Tight symmetry (45 to 55%) available.
- Operation voltage: 1.8V, 2.5V, 3.3V
- Tri-state enable/disable
- RoHS compliant/Pb-free



Electrical Specifications



Parameter	3.3V		2.5V		1.8V		Unit
	Min.	Max.	Min.	Max.	Min.	Max.	
Supply Voltage Variation	3.135	3.465	2.375	2.625	1.71	1.89	V
Frequency Range	1.25	125	1.25	125	1.25	125	MHz
Standard Frequency			4,24,26,32,38,40				MHz
Supply Current(At 15pF Load)	-	15	-	10	-	7	mA
Duty Cycle	45	55	45	55	45	55	%
Transition Time : Rise/Fall Time	1.25 MHz \leq FO < 10MHz 10 MHz \leq FO < 125MHz	-	3	-	4	-	5
Output Level	Out High(Logic "1") Out Low(Logic "0")	2.97 0.33		2.25 0.25		1.62 0.18	V
Start Time	-	2	-	2	-	2	mSec
Tri-State (Input to Pin 1)	Enable(High Voltage or floating) Disable(Low Voltage or GND)	2.31 -	-	1.75 0.75	-	1.26 0.54	V
Period Jitter (Pk-Pk)	-	40	-	40	-	40	pSec
RMS Phase Jitter (integrated 12kHz to 20MHz)	-	1	-	1	-	1	pSec
Standby Current(@-40 to 85°C)	-	10	-	10	-	10	µA
Standby Current(@-40 to 125°C)	-	20	-	20	-	20	µA
Aging(@25 1st year)	-	± 3	-	± 3	-	± 3	ppm
Storage Temp. Range	-55	125	-55	125	-55	125	°C

Standard frequencies are frequencies which the crystal has been designed and does not imply a stock position

.+ Transition times are measured between 10% and 90% of VDD, with an output load of 15pF.

Dimension(mm)

Solder Pad Layout(mm)



To ensure optimal oscillator performance, place a by-pass capacitor of 0.1 µF as close to the part as possible between Vdd and GND pads.

FREQ. STABILITY vs. TEMP. RANGE

Temp. (°C)	± 20	± 25	± 50
-10 ~ +60	o	o	o
-20 ~ +70	△	o	o
-40 ~ +85	x	o	o
-40 ~ +125	x	x	o

o: Available △:Conditional X: Not available

Inclusive of calibration @ 25 °C, operating temperature range, input voltage variation, load variation, aging (1st year), shock, and vibration load variation