## Industry First Low Capacitance ESD Protection Arrays with Backdrive Protection

#### **Product Description**

The CM1223 family of diode arrays has been designed to provide ESD protection for electronic components or subsystems requiring minimal capacitive loading. These devices are ideal for protecting systems with high data and clock rates or for circuits requiring low capacitive loading. Each ESD channel consists of a pair of diodes in series, which steer the positive or negative ESD current pulse to either the positive ( $V_P$ ) or negative ( $V_N$ ) supply rail. A Zener diode is embedded between  $V_P$  and  $V_N$ , to absorb positive ESD strikes and provide ESD protection for the  $V_P$  rail. An additional diode is integrated to serve as backdrive current protection. The CM1223 protects against ESD pulses up to  $\pm 8$  kV per the IEC 61000–4–2 standard. In addition, all pins are protected from contact discharges of greater than  $\pm 15$  kV as outlined by the MIL–STD–883D (Method 3015) specification for Human Body Model (HBM) ESD.

These devices are particularly well-suited for protecting systems using high-speed ports such as USB2.0, IEEE1394 (Firewire<sup>®</sup>, iLink<sup>™</sup>), serial ATA, DVI, HDMI and corresponding ports in removable storage, digital camcorders, DVD-RW drives, as well as other applications where extremely low loading capacitance with ESD protection are required in a small package footprint.

#### Features

- Two, Four, and Eight Channels of ESD Protection with Integrated Backdrive Protection on all Lines
- Provides ESD Protection to IEC61000-4-2 Level 4:
   ±8 kV Contact Discharge & ±15 kV Air Discharge
- Low Channel Input Capacitance of 1.0 pF (typical)
- Minimal Capacitance Change with Temperature and Voltage
- Channel I/O to GND Capacitance Difference of 0.02 pF Typical is Ideal for Differential Signals
- Mutual Capacitance between Signal Pin and Adjacent Signal Pin at 0.11 pF (typical)
- Zener Diode Protects Supply Rail and Eliminates the Need for External Bypass Capacitors
- Pin Compatible with CM1213-02, -04, and -08
- Each I/O Pin Can Withstand over 1000 ESD Strikes
- Available in SOT, and MSOP Packages
- These Devices are Pb-Free and are RoHS Compliant

#### **Applications**

- USB 2.0 Ports at 480 Mbps in Desktop PCs, Notebooks and Peripherals
- IEEE1394 Firewire<sup>®</sup> Ports at 400 Mbps / 800 Mbps
- DVI Ports, HDMI Ports in Notebooks, Set Top Boxes, Digital TVs, LCD Displays



#### ON Semiconductor®

http://onsemi.com





SOT23-5 SO SUFFIX CASE 527AH SOT23-6 SO SUFFIX CASE 527AJ






SOT-143 SR SUFFIX CASE 318A MSOP 10 MR SUFFIX CASE 846AE

#### **BLOCK DIAGRAM**

(see page 2)

#### **MARKING DIAGRAM**



XXX = Specific Device Code

M = Date Code ■ = Pb-Free Package


(Note: Microdot may be in either location)


#### **ORDERING INFORMATION**


Device	Package	Shipping
CM1223-02SO	SOT23-5 (Pb-Free)	3000/Tape & Reel
CM1223-02SR	SOT143-4 (Pb-Free)	3000/Tape & Reel
CM1223-04SO	SOT23-6 (Pb-Free)	3000/Tape & Reel
CM1223-04MR	MSOP-10 (Pb-Free)	4000/Tape & Reel
CM1223-08MR	MSOP-10 (Pb-Free)	4000/Tape & Reel

- †For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.
- UDI and Display Ports
- Serial ATA Ports in Desktop PCs and Hard Disk Drives
- PCI Express Ports
- General Purpose High-speed Data Line ESD Protection

#### **BLOCK DIAGRAM**







**Table 1. PIN DESCRIPTIONS** 

	2-Channel, 5-Lead SOT23-5 Package					
Pin Name Type Description		Description				
1	NC		No Connect			
2	V <sub>N</sub>	GND	Negative voltage supply rail			
3	CH1	I/O	ESD Channel			
4	CH2	I/O	ESD Channel			
5	V <sub>P</sub>	PWR	Positive voltage supply rail			


	4-Channel, 6-Lead SOT23-6 Package					
Pin	Name	Type	Description			
1	CH1	I/O	ESD Channel			
2	V <sub>N</sub>	GND	Negative voltage supply rail			
3	CH2	I/O	ESD Channel			
4	СНЗ	I/O	ESD Channel			
5	V <sub>P</sub>	PWR	Positive voltage supply rail			
6	CH4	I/O	ESD Channel			


4-Channel, 10-Lead MSOP-10 Package					
Pin	Name	Туре	Description		
1	CH1	I/O	ESD Channel		
2	NC		No Connect		
3	V <sub>P</sub>	PWR	Positive voltage supply rail		
4	CH2	I/O	ESD Channel		
5	NC		No Connect		
6	СНЗ	I/O	ESD Channel		
7	NC		No Connect		
8	V <sub>N</sub>	GND	Negative voltage supply rail		
9	CH4	I/O	ESD Channel		
10	NC		No Connect		


	8-Channel, 10-Lead MSOP-10 Package					
Pin	Name	Туре	Description			
1	CH1	I/O	ESD Channel			
2	CH2	I/O	ESD Channel			
3	СНЗ	I/O	ESD Channel			
4	CH4	I/O	ESD Channel			
5	V <sub>N</sub>	GND	Negative voltage supply rail			
6	CH5	I/O	ESD Channel			
7	CH6	I/O	ESD Channel			
8	V <sub>P</sub>	PWR	Positive voltage supply rail			
9	CH7	I/O	ESD Channel			
10	CH8	I/O	ESD Channel			


	2-Channel, 4-Lead SOT143-4 Package					
Pin	Name	Type	Description			
1	V <sub>N</sub>	GND	Negative voltage supply rail			
2	CH1	I/O	ESD Channel			
3	CH2	I/O	ESD Channel			
4	V <sub>P</sub>	PWR	Positive voltage supply rail			

#### PACKAGE / PINOUT DIAGRAMS









10-Lead MSOP-10

Тор	o Vi	ew			
CH1   1 CH2   2 CH3   3 CH4   4 V <sub>N</sub>   5	D336	10 9 8 7 6	Ш	CH8 CH7 V <sub>P</sub> CH6 CH5	
10-Lead MSOP-10					

#### **SPECIFICATIONS**

**Table 2. ABSOLUTE MAXIMUM RATINGS** 

Parameter	Rating	Units
Operating Supply Voltage (V <sub>P</sub> – V <sub>N</sub> )	6.0	V
Operating Temperature Range	-40 to +85	°C
Storage Temperature Range	−65 to +150	°C
DC Voltage at any channel input	(V <sub>N</sub> – 0.5) to (V <sub>P</sub> + 0.5)	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### **Table 3. STANDARD OPERATING CONDITIONS**

Parameter	Rating	Units
Operating Temperature Range	-40 to +85	°C
Package Power Rating SOT143-4 Package (CM1223-02SR) SOT23-5 Package (CM1223-02SO) SOT23-6 Package (CM1223-04SO) MSOP-10 Package (CM1223-04MR) MSOP-10 Package (CM1223-08MR)	225 225 225 400 400	mW


#### Table 4. ELECTRICAL OPERATING CHARACTERISTICS (Note1)

Symbol	Parameter	Conditions	Min	Тур	Max	Units
$V_{P}$	Operating Supply Voltage (V <sub>P</sub> -V <sub>N</sub> )			3.3	5.5	V
Ι <sub>Ρ</sub>	Operating Supply Current	$(V_P - V_N) = 3.3 \text{ V}$			8.0	μΑ
V <sub>SCL</sub>	Signal Clamp Voltage Positive Transients Negative Transients	I <sub>F</sub> = 8 mA; T <sub>A</sub> = 25°C	6.7 0.60	8.2 0.80		٧
I <sub>LEAK</sub>	Channel Leakage Current	T <sub>A</sub> = 25°C; V <sub>P</sub> = 5 V, V <sub>N</sub> = 0 V		±0.1	±1.0	μΑ
C <sub>IN</sub>	Channel Input Capacitance	At 1 MHz, V <sub>P</sub> = 3.3 V, V <sub>N</sub> = 0 V, V <sub>IN</sub> = 1.65 V		1.0	1.5	pF
$\Delta C_{IN}$	Channel Input Capacitance Matching	At 1 MHz, V <sub>P</sub> = 3.3 V, V <sub>N</sub> = 0 V, V <sub>IN</sub> = 1.65 V		0.02		pF
C <sub>MUTUAL</sub>	Mutual Capacitance between signal pin and adjacent signal pin	At 1 MHz, V <sub>P</sub> = 3.3 V, V <sub>N</sub> = 0 V, V <sub>IN</sub> = 1.65 V		0.11		pF
V <sub>ESD</sub>	ESD Protection – Peak Discharge Voltage at any channel input, in system a) Contact discharge per IEC 61000–4–2 standard b) Human Body Model, MIL–STD–883, Method 3015	T <sub>A</sub> = 25°C; (Notes 3 and 4) T <sub>A</sub> = 25°C; (Notes 2 and 4)	±8 ±15			kV
V <sub>CL</sub>	Channel Clamp Voltage Positive Transients Negative Transients	$T_A = 25^{\circ}C$ , $I_{PP} = 1A$ , $t_P = 8/20 \ \mu S$ (Note 4)		+8.8 -1.4		٧
R <sub>DYN</sub>	Dynamic Resistance Positive Transients Negative Transients	$T_A$ = 25°C, Ipp = 1A, tp = 8/20 $\mu S$ Any I/O pin to Ground (Note 4)		0.7 0.4		Ω

- 1. All parameters specified at  $T_A = -40^{\circ}C$  to  $+85^{\circ}C$  unless otherwise noted. 2. Human Body Model per MIL-STD-883, Method 3015,  $C_{Discharge} = 100$  pF,  $R_{Discharge} = 1.5$  k $\Omega$ ,  $V_P = 3.3$  V,  $V_N$  grounded. 3. Standard IEC 61000-4-2 with  $C_{Discharge} = 150$  pF,  $R_{Discharge} = 330$   $\Omega$ ,  $V_P = 3.3$  V,  $V_N$  grounded. 4. These measurements performed with no external capacitor on  $V_P$  ( $V_P$  floating).


#### PERFORMANCE INFORMATION

#### **Input Channel Capacitance Performance Curves**



Typical Variation of  $C_{\text{IN}}$  vs.  $V_{\text{IN}}$ 

(f=1MHz,  $V_P$  = 3.3V,  $V_N$  = 0V, 0.1  $\mu F$  chip capacitor between  $V_P$  and  $V_{N_c}$  25°C)



Typical Variation of C<sub>IN</sub> vs. Temp

(f=1MHz,  $V_{IN}$ =30mV,  $V_P$  = 3.3V,  $V_N$  = 0V, 0.1  $\mu$ F chip capacitor between  $V_P$  and  $V_N$ )

#### PERFORMANCE INFORMATION (Cont'd)

Typical Filter Performance (nominal conditions unless specified otherwise, 50 Ohm Environment)




Figure 1. Insertion Loss (S21) vs. Frequency (0 V DC Bias, V<sub>P</sub>=3.3 V, MSOP-10 Package)




Figure 2. Insertion Loss (S21) vs. Frequency (2.5 V DC Bias, V<sub>P</sub>=3.3 V, MSOP-10 Package)

#### **BACKDRIVE PROTECTION**

Backdrive protection is needed to block against backdrive current flowing from a high potential voltage node toward a lower potential voltage node through the interface cable.

For example, consider a DVD player connected to a TV via an HDMI interface. If the DVD player is switched off and the TV is left on, there is a possibility of reverse current flow back into the main power supply rail of the DVD player. Typically, the DVD's power supply has some form of associated bulk supply capacitance, and it is possible over time to charge that bulk supply capacitance to some intermediate level.

If that level rises above the power-on-reset (POR) voltage level of some of the integrated circuits, the DVD player may not reset properly when the DVD player is turned back on. This is largely because all CMOS logic exhibits a very high impedance on the power rail node even when "off".

To avoid this situation, the CM1223 with integrated backdrive protection diode was designed to block backdrive current, guaranteeing no more than 5  $\mu$ A on any I/O pin when the I/O pin voltage is greater than the CM1223 supply voltage.

#### **APPLICATION INFORMATION**

#### **Design Considerations**

To realize the maximum protection against ESD pulses, care must be taken in the PCB layout to minimize parasitic series inductances on the Supply/Ground rails as well as the signal trace segments between the signal input (typically a connector) and the ESD protection device. Application of Positive ESD Pulse between Input Channel and Ground illustrates an example of a positive 8 kV ESD pulse striking an input channel. The 8 kV ESD current pulse will divert along the path as indicated in Application of Positive ESD Pulse between Input Channel and Ground, through the D1 diode and the Zener diode back to the ground rail.

An ESD current pulse can rise from zero to its peak value in a very short time. For example, a level 4 contact discharge per the IEC61000–4–2 standard results in a current pulse that rises from zero to 30 Amps in 1ns. The CM1223 has a fast response time of less than 1ns and low clamp voltage to handle this pulse scenario.

Similarly for negative ESD pulses, parasitic series inductance from the  $V_N$  pin to the ground rail will lead to drastically increased negative voltage on the line being protected.

The CM1223 also has an integrated backdrive diode between  $V_P$  and  $V_N$  to prevent backdrive current flow from the powered sources.

As a general rule, the ESD Protection Array should be located as close as possible to the point of entry of expected electrostatic discharges.

#### **ADDITIONAL INFORMATION**

See also ON Semiconductor Application Note "Design Considerations for ESD Protection", in the Applications section.




Figure 3. Application of Positive ESD Pulse between Input Channel and Ground




Figure 4. Application of Positive ESD Pulse between Input Channel and Ground

#### **MECHANICAL DETAILS**


The CM1223 is available in SOT143-4, SOT23-5, SOT23-6, and MSOP-10 packages with a lead-free finishing. The various package drawings are presented below.

#### **SOT143 Mechanical Specifications**

The CM1223–02SR is supplied in 4-pin SOT143 package, the CM1223–02SO in a 5-pin SOT23 package, the CM1223–04SO in a 6-pin SOT23 package, and the CM1223–08MR in a 10-lead MSOP package. Dimensions are presented below.

**Table 5. TAPE AND REEL SPECIFICATIONS** 

Part Number	Chip Size (mm)	Pocket Size (mm) B <sub>0</sub> X A <sub>0</sub> X K <sub>0</sub>	Tape Width W	Reel Diameter	Qty per Reel	P <sub>0</sub>	P <sub>1</sub>
CM1223-02SR	2.92 X 2.37 X 1.01	2.60 X 3.15 X1.20	8 mm	178 mm (7")	3000	4 mm	4 mm
CM1223-02SO	2.90 X 2.80 X 1.45	3.20 X 3.20 X1.40	8 mm	178 mm (7")	3000	4 mm	4 mm
CM1223-04SO	2.90 X 2.80 X 1.45	3.20 X 3.20 X1.40	8 mm	178 mm (7")	3000	4 mm	4 mm
CM1223-08MR	3.00 X 3.00 X 0.85	3.30 X 5.30 X1.30	12 mm	330 mm (13")	4000	4 mm	8 mm





iLink  $^{\sim}$  is a trademark of S.J.Electro Systems, Inc. FireWire $^{\odot}$  is a registered trademark of Apple Computer, Inc.




SOT-143 CASE 318A-06 **ISSUE U** 

**DATE 07 SEP 2011** 








#### NOTES:

- OLES.

  1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: MILLIMETERS.
  3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIM-UM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, AND GATE BURRS SHALL NOT EXCEED 0.25 PER SIDE. DI-MENSION E1 DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH AND PROTRUSION SHALL NOT EXCEED 0.25 PER SIDE.
  5. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H.
  6. DATUMS A AND B ARE DETERMINED AT DATUM H.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.80	1.12	
A1	0.01	0.15	
b	0.30	0.51	
b1	0.76	0.94	
С	0.08	0.20	
D	2.80	3.05	
E	2.10	2.64	
E1	1.20	1.40	
е	1.92	BSC	
e1	0.20 BSC		
L	0.35	0.70	
L2	0.25	BSC	

#### **RECOMMENDED SOLDERING FOOTPRINT**



DIMENSIONS: MILLIMETERS

#### **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code

= Date Code

= Pb-Free Package

(Note: Microdot may be in either location)


\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 2:	STYLE 3:	STYLE 4:	STYLE 5:	STYLE 6:
PIN 1. SOURCE	PIN 1. GROUND	PIN 1. OUTPUT	PIN 1. SOURCE	PIN 1. GND
2. DRAIN	2. SOURCE	2. GROUND	2. DRAIN	2. RF IN
3. GATE 1	3. INPUT	<ol><li>GROUND</li></ol>	3. GATE 1	3. VREG
4. GATE 2	4. OUTPUT	4. INPUT	4. SOURCE	<ol><li>RF OUT</li></ol>
STYLE 8: PIN 1. SOURCE 2. GATE 3. DRAIN 4. N/C	STYLE 9: PIN 1. GND 2. IOUT 3. VCC 4. VREF	STYLE 10: PIN 1. DRAIN 2. N/C 3. SOURCE 4. GATE	STYLE 11: PIN 1. SOURCE 2. GATE 1 3. GATE 2 4. DRAIN	
	PIN 1. SOURCE 2. DRAIN 3. GATE 1 4. GATE 2 STYLE 8: PIN 1. SOURCE 2. GATE 3. DRAIN	PIN 1. SOURCE 2. DRAIN 2. SOURCE 3. GATE 1 3. INPUT 4. GATE 2 4. OUTPUT   STYLE 8: STYLE 9: PIN 1. SOURCE PIN 1. GND 2. GATE 2. IOUT 3. DRAIN 3. VCC	PIN 1. SOURCE	PIN 1. SOURCE

DOCUMENT NUMBER:	98ASB42227B	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SOT-143		PAGE 1 OF 1

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.






SOT-23, 5 Lead CASE 527AH **ISSUE A** 


**DATE 09 JUN 2021** 

#### NUTES


- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 19894
- CONTROLLING DIMENSION: MILLIMETERS
- MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE
- DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS, MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.25 PER SIDE. D AND E1 DIMENSIONS ARE DETERMINED AT DATUM D.
- DIMENSION 'b' DOES NOT INCLUDE DAMBAR PROTRUSION. DAMBAR PROTRUSION SHALL BE O. 08mm TOTAL IN EXCESS OF THE 'b' DIMENSION AT MAXIMUM MATERIAL CONDITION. MINIMUM SPACE BETWEEN PROTRUSION AND AN ADJACENT LEAD SHALL NOT BE LESS THAN 0.07mm.




TOP VIEW



# END VIEW





#### **GENERIC MARKING DIAGRAM\***



XXX = Specific Device Code = Date Code


\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "=", may or may not be present. Some products may not follow the Generic Marking.

#### RECOMMENDED MOUNTING FOOTPRINT


For additional information on our Pb-Free strategy and soldering details, please download the  $\square N$  Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


DOCUMENT NUMBER:	98AON34320E	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SOT-23, 5 LEAD		PAGE 1 OF 1

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the





**DATE 29 FEB 2012** 





NOTES:






## GENERIC MARKING DIAGRAM\*

0.95 BSC

0.20 0.60



XXX = Specific Device Code


M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " •", may or may not be present.

### RECOMMENDED SOLDERING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

DOCUMENT NUMBER:	98AON34321E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SOT-23, 6 LEAD		PAGE 1 OF 1


ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.


<sup>\*</sup>For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




MSOP10, 3x3 CASE 846AE **ISSUE A** 

**DATE 20 JUN 2017** 





#### RECOMMENDED **SOLDERING FOOTPRINT\***



**DIMENSIONS: MILLIMETERS** 

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### NOTES:

- DIMENSIONS AND TOLERANCING PER ASME Y14.5M, 1994.
  CONTROLLING DIMENSIONS: MILLIMETERS.
  DIMENSION 6 DOES NOT INCLUDE DAMBAR PROTRUSION.
  ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.10 MM IN
- ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.10 MM IN EXCESS OF MAXIMUM MATERIAL CONDITION.
  DIMENSION D DOES NOT INCLUDE MOLD FLASH,
  PROTRUSIONS, OR GATE BURRS. MOLD FLASH,
  PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15
  MM PER SIDE. DIMENSION E DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR
  PROTRUSION SHALL NOT EXCEED 0.25 MM PER SIDE.
  DIMENSIONS DANDE ARE DETERMINED AT DATUME.
- DIMENSIONS D AND E ARE DETERMINED AT DATUM F. DATUMS A AND B TO BE DETERMINED AT DATUM F.
- A1 IS DEFINED AS THE VERTICAL DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE

	MILLIMETERS			
DIM	MIN	NOM	MAX	
Α			1.10	
A1	0.00	0.05	0.15	
A2	0.75	0.85	0.95	
b	0.17		0.27	
C	0.13		0.23	
D	2.90	3.00	3.10	
Е	4.75	4.90	5.05	
E1	2.90	3.00	3.10	
е	0.50 BSC			
L	0.40	0.70	0.80	
L1	0.95 REF			
L2	0.25 BSC			
θ	0°		8°	

#### **GENERIC MARKING DIAGRAM\***



XXXX = Specific Device Code = Assembly Location Α

Υ = Year W = Work Week = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present and may be in either location. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON34098E	Electronic versions are uncontrolled except when accessed directly from the Document Repositor, Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	MSOP10, 3X3		PAGE 1 OF 1

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales