

NCP57302DSADGEVB:3.0 A Adjustable VLDO Regulator Evaluation Board

Evaluation Board Description

The NCP57302 is a high precision, very low dropout (VLDO), low minimum input voltage and low ground current positive voltage regulator that is capable of providing an output current in excess of 3.0 A with a typical dropout voltage of 315 mV at 3.0 A load current and input voltage from 1.8 V and up. The device is stable with ceramic output capacitors. The device can withstand up to 18 V max input voltage. Internal protection features consist of output current limiting, built-in thermal shutdown and reverse output current protection. Logic level enable pin is available. The NCP57302 is an adjustable voltage device and is available in D2PAK-5 package.



Design Support

Technical

- Documentation
- » Design Resources
- Technical Support
- Sales Support

Evaluation Board Information

Evaluation Board	Status		Short Description	Parts Used	Action
NCP57302DSADGEVB	Active	⊛	3.0 A Adjustable VLDO Regulator Evaluation Board	NCP57302DSADJR4G	

Technical Documents						
Туре	Document Title	Document ID/Size	Rev			
Eval Board: BOM	NCP57302DSADGEVB Bill of Materials ROHS Compliant	NCP57302DSADGEVB_BOM_ROHS.PDF - 43.0 KB	0			
Eval Board: Gerber	NCP57302DSADGEVB Gerber Layout Files (Zip Format)	NCP57302DSADGEVB_GERBER.ZIP - 28.0 KB	0			
Eval Board: Schematic	NCP57302DSADGEVB Schematic	NCP57302DSADGEVB_SCHEMATIC.PDF - 40.0 KB	0			
Eval Board: Test Procedure	NCP57302DSADGEVB Test Procedure	NCP57302DSADGEVB_TEST_PROCEDURE.PDF - 52.0 KB	0			

Privacy Policy | Terms of Use | Site Map | Careers | Contact Us | Terms and Conditions | Mobile Portal

Copyright © 1999-2013 ON Semiconductor

Follow Us 🛛 🔝 🔡 💽

http://www.onsemi.com/PowerSolutions/evalBoard.do?id=NCP57302DSADGEVB[7/8/2013 2:53:06 PM]