


A
B
C
D
E
F



ITEM No.	PART NAME	PART No.	CODE No.
1, 2, 3	CONNECTOR UNIT	DF56-40P-0.3SD(51)	CL662-5601-3-51
—	METAL SHIELDING	DF56-40P-SHL	CL662-5602-6-00

NOTES

1. APPLICABLE CABLE: MICRO COAXIAL CABLE(AWG#42~AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS 'CONNECTOR UNIT, AND METAL SHIELDING'. REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No AND CODE No.
4. SOLDER A GRAND BAR WITH AN EXTERNAL CONDUCTOR OF THE CABLE ABOUT STICKING A GRAND BAR TOGETHER.
5. PLEASE CONSULT ABOUT THE USE OF THE POTTING AND KAPTON TAPE SEPARATELY.

2	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.1μm min TERMINATION AREA : Au PLATING 0.1μm min UNDER PLATING : Ni PLATING 1μm min	6	PS	BLACK
			5	POLYESTER	CLEAR
			4	PS	CLEAR
			3	STAINLESS	WHOLE AREA : Sn PLATING 1μm min UNDER PLATING : Ni 0.2μm min
1	LCP	UL94V-0 , BLACK			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm					
SCALE FREE			COUNT 		
			DESCRIPTION OF REVISIONS DIS-H-005089		
			DESIGNED AH.MIYAZAKI		
			CHECKED IO.DENPOUYA		
			DATE 10.09.15		
APPROVED : TS. SAKATA			DRAWING NO. EDC3-324301-01		
CHECKED : IO.DENPOUYA			PART NO. DF56-40P-0.3SD(51)		
DESIGNED : AH.MIYAZAKI			CODE NO. CL662-5601-3-51		
DRAWN : AH.MIYAZAKI					

A
B
C
D
E
F

