





Mark	ECN NO.	DESCRIPTION	DESIGN	Date:



P.C.B. LAYOUT(TOP VIEW)

NOTE:

BODY: PBT+30%G.F UL94V-0
 SPACER: PA66+30%G.F UL94V-0
 CONTACTS: COPPER ALLOY
 CONTACT : COPPER ALLOY
 CONTACT : UNDER PLATED NICKEL,
 OVER ALL TIN IN SOLDERING AREA,
 SELECTIVE GOLD PLATED IN CONTACT AREA.

SHIELD : SPCC T=0.5
 SHIELD : NICKEL PLATED.
 UNDER PLATED Cu.

BOARD LOCK:SPCC ,Tin PLATED.
 RIVET : COPPER ALLOY , NICKEL PLATED.
 SCREW : Fe,NICKEL PLATED.

*MECHANICAL

MATING FORCE: 4.5 KG MAX. 25 MM/MINUTE
 UNMATING FORCE: 1.0-4.0 KG MIN.
 DURABILITY: 100 MATING CYCLES

*ELECTRICAL SPECIFICATION

INSULATION RESISTANCE: 1000 MEGOHMS MIN
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC RMS±50V.60 HZ
 CURRENT RATING: 1.5 AMPERES MIN

*ENVIRONMENTAL

OPERATING TEMPERATURE: -20℃ to 85℃

Tolerance	Model Name: DVI 24+5PIN 锁铆4.8螺母				Drawing: Zengling
X.X ±0.25	Model No: XDVF-0934-0246				Checked: Lijian
X.XX ±0.15	UNIT:	SCALE:	REVISION:	SHEET	Approved: WEI JI YANG
X.XXX ±0.10	mm	FULL	A1	1/1	Date: 2011.08.23
Angle ±2.0°	深圳市连欣科技有限公司				DWG NO.
					FILE: C