


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


| REVISIONS |                 |            |           |
|-----------|-----------------|------------|-----------|
| REV       | DESCRIPTION     | DATE       | APPROVED  |
| A         | INITIAL RELEASE | 03/15/2021 | PHOSPODAR |
|           |                 |            |           |
|           |                 |            |           |
|           |                 |            |           |

|   |    | WIRING MAP      |    |    |    |
|---|----|-----------------|----|----|----|
| D | J1 | COLOR           | J2 | J3 | J4 |
|   | 1  | BLUE            | 12 |    |    |
|   | 2  | ORANGE          | 11 |    |    |
|   | 3  | GREEN           | 10 |    |    |
|   | 4  | BROWN           | 9  |    |    |
|   | 5  | GRAY            |    | 12 |    |
|   | 6  | WHITE           |    | 11 |    |
|   | 7  | RED             |    | 10 |    |
|   | 8  | BLACK           |    | 9  |    |
|   | 9  | YELLOW          |    |    | 12 |
| C | 10 | PURPLE          |    |    | 11 |
|   | 11 | ROSE            |    |    | 10 |
|   | 12 | AQUA            |    |    | 9  |
|   | 13 | BLUE w/TRACER   | 1  |    |    |
|   | 14 | ORANGE w/TRACER | 2  |    |    |
| → | 15 | GREEN w/TRACER  | 3  |    |    |
|   | 16 | BROWN w/TRACER  | 4  |    |    |
|   | 17 | GRAY w/TRACER   |    | 1  |    |
|   | 18 | WHITE w/TRACER  |    | 2  |    |
|   | 19 | RED w/TRACER    |    | 3  |    |
| B | 20 | BLACK w/TRACER  |    | 4  |    |
|   | 21 | YELLOW w/TRACER |    |    | 1  |
|   | 22 | PURPLE w/TRACER |    |    | 2  |
|   | 23 | ROSE w/TRACER   |    |    | 3  |
|   | 24 | AQUA w/TRACER   |    |    | 4  |



NOTES:

1. MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|                                                                                                                                                                                                                                                   |  |                                                 |  |                                                                |                           |                                                                                                             |  |                                                                                                      |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------|--|----------------------------------------------------------------|---------------------------|-------------------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]                                                                                                                                                                                      |  | APPROVALS                                       |  | DATE                                                           |                           | <br>an INFINITE™ brand |  | 50 High Street, West Mill,<br>North Andover, MA 01845 USA<br>Phone: 1.800.341.5266<br>1.978.682.6936 |  |
| OVERALL CABLE LENGTH TOLERANCE:<br>$\leq 12$ [305] = +1 [25] / -0<br>$>12$ [305] $\leq 60$ [1524] = +2 [51] / -0<br>$>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0<br>$>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0<br>$>300$ [7620] = +5% / -0 |  | DRAWN BY<br>DZINN                               |  | 03/15/2021                                                     |                           | CATEGORY                                                                                                    |  | FIBER OPTIC                                                                                          |  |
|                                                                                                                                                                                                                                                   |  | CHECKED BY<br>DFRISIELLO                        |  | 03/15/2021                                                     |                           |                                                                                                             |  |                                                                                                      |  |
|                                                                                                                                                                                                                                                   |  | APPROVED BY<br>PHOSPODAR                        |  | 03/15/2021                                                     |                           |                                                                                                             |  |                                                                                                      |  |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>$.X = \pm .2$ [5]<br>$.XX = \pm .02$ [.5]<br>$.XXX = \pm .005$ [.13]                                                                                                                                         |  | FRACTIONS<br>$\pm 1/32$<br>ANGLES $\pm 1^\circ$ |  | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY |                           | PRODUCT DESCRIPTION<br>FIBER AG CONV HARNESS,<br>MPO24 (F) TO 3XMP08 (F)                                    |  |                                                                                                      |  |
| THIRD-ANGLE PROJECTION<br>                                                                                                                                   |  | COLOR VARIATIONS<br>MAY OCCUR                   |  | SIZE<br><b>A</b>                                               | GAGE CODE<br><b>43321</b> | ITEM NO.<br>MPF24308OM5R-CA                                                                                 |  | REV<br><b>A</b>                                                                                      |  |
|                                                                                                                                                                                                                                                   |  |                                                 |  | SCALE: NONE                                                    |                           | CAD FILE: MPF24308OM5R-CA.SLDRW                                                                             |  | SHEET 1 OF                                                                                           |  |