







RoHS Compliant



- NOTE:
1. MATERIAL:
- 1.1 INSULATOR: LCP UL 94V-0 蓝
 - 1.2 CONTACT: C5191 (T=0.20mm)
 - 1.3 SHELL: C2680 (T=0.30mm)
2. ELECTRICAL CHARACTERISTICS:
- 2.1 CONTACT RESISTANCE: 30mΩ MAXIMUM
 - 2.2 CONTACT CURRENT RATING: 1.5A
 - 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 500 V R.M.S.
 - 2.4 INSULATION RESISTANCE 1000 MEGOHMS MIN
 - 2.5 OPERATING TEMPERATURE: -40° C ~ 85° C
3. MECHANICAL CHARACTERISTICS:
- 3.1 MATING FORCE: 3.57kg MAX
 - 3.2 UNMATED FORCE: 1.02kg MIN
 - 3.3 DURABILITY: MANDATORY: 5,000 CYCLES
4. PLATING
- 4.1 TERMINAL:
- 50u" MIN NICKEL ALL OVER
100u" MIN TIN ON SOLDER AREA
(1~30)u" Au ON CONTACT AREA
- 4.2 SHELL: 100u" MIN. NICKEL ALL OVER
5. "▲" FOR MAJOR DIM



深圳市连欣科技有限公司

04	Molding件	LCP	1	颜色, UL94 V-0	
03	外壳	C2680, T=0.30	1	镀镍	
01	端子	C5191, T=0.20	1set	功能接触区镀金, 焊脚镀锡	
序号	料号	品名	材质	用量	备注

品名 (ITEM NO)	USB 3.0 A 母座 成品
料号 (PART NO)	XUSF-0922-063
模号 (MODEL NO)	N/A
图号 (DWG NO)	
版本 (REV)	A/0
日期 (DATE)	2015.06.09
设计 (DESIGN)	
审核 (CHECKED)	~
核准 (APPROVED)	
单位 (UNIT): MM	
比例 (SCALE) 1:1	
公差 (TOLERANCE UNSPECIFIED)	X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 X.X° ±2°

由 Autodesk 教育版产品制作