



T-46-07-11

MM54HC273/MM74HC273

## MM54HC273/MM74HC273 Octal D Flip-Flops with Clear

### General Description

These edge triggered flip-flops utilize advanced silicon-gate CMOS technology to implement D-type flip-flops. They possess high noise immunity, low power, and speeds comparable to low power Schottky TTL circuits. This device contains 8 master-slave flip-flops with a common clock and common clear. Data on the D input having the specified setup and hold times is transferred to the Q output on the low to high transition of the CLOCK input. The CLEAR input when low, sets all outputs to a low state.


Each output can drive 10 low power Schottky TTL equivalent loads. The MM54HC273/MM74HC273 is functionally

as well as pin compatible to the 54LS273/74LS273. All inputs are protected from damage due to static discharge by diodes to V<sub>CC</sub> and ground.

### Features

- Typical propagation delay: 18 ns
- Wide operating voltage range
- Low input current: 1  $\mu$ A maximum
- Low quiescent current: 80  $\mu$ A (74 Series)
- Output drive: 10 LS-TTL loads

### Connection Diagram



Order Number MM54HC273\* or MM74HC273\*

\*Please look into Section 8, Appendix D for availability of various package types.

3

### Truth Table

(Each Flip-Flop)

| Inputs |       | Outputs |                |
|--------|-------|---------|----------------|
| Clear  | Clock | D       | Q              |
| L      | X     | X       | L              |
| H      | ↑     | H       | H              |
| H      | ↑     | L       | L              |
| H      | L     | X       | Q <sub>0</sub> |

H = high level (steady state)

L = low level (steady state)

X = don't care

↑ = transition from low to high level

Q<sub>0</sub> = the level of Q before the indicated steady state  
Input conditions were established

T-46-07-11

MM54HC273/MM74HC273

**Absolute Maximum Ratings** (Notes 1 and 2)

If Military/Aerospace specified devices are required, contact the National Semiconductor Sales Office/Distributors for availability and specifications.

|   |                               |
|---|-------------------------------|
| Supply Voltage (V <sub>CC</sub> )                             | -0.5 to +7.0V                 |
| DC Input Voltage (V <sub>IN</sub> )                           | -1.5 to V <sub>CC</sub> +1.5V |
| DC Output Voltage (V <sub>OUT</sub> )                         | -0.5 to V <sub>CC</sub> +0.5V |
| Clamp Diode Current (I <sub>IK</sub> , I <sub>OK</sub> )      | ±20 mA                        |
| DC Output Current, per pin (I <sub>OUT</sub> )                | ±25 mA                        |
| DC V <sub>CC</sub> or GND Current, per pin (I <sub>CC</sub> ) | ±50 mA                        |
| Storage Temperature Range (T <sub>STG</sub> )                 | -65°C to +150°C               |
| Power Dissipation (P <sub>D</sub> )<br>(Note 3)               | 600 mW                        |
| S.O. Package only   | 500 mW                        |
| Lead Temp. (T <sub>L</sub> ) (Soldering 10 seconds)           | 260°C                         |

**Operating Conditions**

|   | Min                   | Max             | Units |
|---|-----------------------|-----------------|-------|
| Supply Voltage (V <sub>CC</sub> )                                   | 2                     | 6               | V     |
| DC Input or Output Voltage<br>(V <sub>IN</sub> , V <sub>OUT</sub> ) | 0                     | V <sub>CC</sub> | V     |
| Operating Temp. Range (T <sub>A</sub> )                             |                       |                 |       |
| MM74HC  | -40                   | +85             | °C    |
| MM54HC  | -55                   | +125            | °C    |
| Input Rise or Fall Times<br>(t <sub>r</sub> , t <sub>f</sub> )      | V <sub>CC</sub> =2.0V | 1000            | ns    |
|   | V <sub>CC</sub> =4.5V | 500             | ns    |
|   | V <sub>CC</sub> =6.0V | 400             | ns    |

**DC Electrical Characteristics** (Note 4)

| Symbol          | Parameter                         | Conditions  | V <sub>CC</sub> | T <sub>A</sub> =25°C |                   | 74HC<br>T <sub>A</sub> =-40 to 85°C | 54HC<br>T <sub>A</sub> =-55 to 125°C | Units |
|-----------------|-----------------------------------|---|-----------------|----------------------|-------------------|-------------------------------------|--------------------------------------|-------|
|                 |                                   |   |                 | Typ                  | Guaranteed Limits |                                     |                                      |       |
| V <sub>IH</sub> | Minimum High Level Input Voltage  |   | 2.0V            | 1.5                  | 1.5               | 1.5                                 | 1.5                                  | V     |
|                 |                                   |   | 4.5V            | 3.15                 | 3.15              | 3.15                                | 3.15                                 | V     |
|                 |                                   |   | 6.0V            | 4.2                  | 4.2               | 4.2                                 | 4.2                                  | V     |
| V <sub>IL</sub> | Maximum Low Level Input Voltage** |   | 2.0V            | 0.5                  | 0.5               | 0.5                                 | 0.5                                  | V     |
|                 |                                   |   | 4.5V            | 1.35                 | 1.35              | 1.35                                | 1.35                                 | V     |
|                 |                                   |   | 6.0V            | 1.8                  | 1.8               | 1.8                                 | 1.8                                  | V     |
| V <sub>OH</sub> | Minimum High Level Output Voltage | V <sub>IN</sub> =V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>  ≤20 μA                              | 2.0V            | 2.0                  | 1.9               | 1.9                                 | 1.9                                  | V     |
|                 |                                   |   | 4.5V            | 4.5                  | 4.4               | 4.4                                 | 4.4                                  | V     |
|                 |                                   |   | 6.0V            | 6.0                  | 5.9               | 5.9                                 | 5.9                                  | V     |
| V <sub>OL</sub> | Maximum Low Level Output Voltage  | V <sub>IN</sub> =V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>  ≤20 μA                              | 2.0V            | 0                    | 0.1               | 0.1                                 | 0.1                                  | V     |
|                 |                                   |   | 4.5V            | 0                    | 0.1               | 0.1                                 | 0.1                                  | V     |
|                 |                                   |   | 6.0V            | 0                    | 0.1               | 0.1                                 | 0.1                                  | V     |
|                 |                                   | V <sub>IN</sub> =V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>  ≤4 mA<br> I <sub>OUT</sub>  ≤5.2 mA | 4.5V            | 4.2                  | 3.98              | 3.84                                | 3.7                                  | V     |
|                 |                                   |   | 6.0V            | 5.7                  | 5.48              | 5.34                                | 5.2                                  | V     |
| I <sub>IN</sub> | Maximum Input Current             | V <sub>IN</sub> =V <sub>CC</sub> or GND   | 6.0V            |                      | ±0.1              | ±1.0                                | ±1.0                                 | μA    |
| I <sub>CC</sub> | Maximum Quiescent Supply Current  | V <sub>IN</sub> =V <sub>CC</sub> or GND<br>I <sub>OUT</sub> =0 μA   | 6.0V            |                      | 8                 | 80                                  | 160                                  | μA    |

Note 1: Absolute Maximum Ratings are those values beyond which damage to the device may occur.

Note 2: Unless otherwise specified all voltages are referenced to ground.

Note 3: Power Dissipation (temperature derating) — plastic "N" package: -12 mW/°C from 65°C to 85°C; ceramic "J" package: -12 mW/°C from 100°C to 125°C.

Note 4: For a power supply of 5V ±10% the worst case output voltages (V<sub>OH</sub> and V<sub>OL</sub>) occur for HC at 4.5V. Thus the 4.5V values should be used when designing with this supply. Worst case V<sub>IH</sub> and V<sub>IL</sub> occur at V<sub>CC</sub>=5.5V and 4.5V respectively. (The V<sub>IH</sub> value at 5.5V is 3.85V.) The worst case leakage current (I<sub>IN</sub>, I<sub>CC</sub>, and I<sub>OZ</sub>) occur for CMOS at the higher voltage and so the 6.0V values should be used.

\*\*V<sub>IL</sub> limits are currently tested at 20% of V<sub>CC</sub>. The above V<sub>IL</sub> specification (30% of V<sub>CC</sub>) will be implemented no later than Q1, CY'89.

T-46-07-11

**AC Electrical Characteristics**  $V_{CC}=5V$ ,  $T_A=25^\circ C$ ,  $C_L=15\text{ pF}$ ,  $t_r=t_f=6\text{ ns}$ 

MM54HC273/MM74HC273

| Symbol             | Parameter                                  | Conditions | Typ | Guaranteed Limit | Units |
|--------------------|--|------------|-----|------------------|-------|
| $f_{MAX}$          | Maximum Operating Frequency                |            | 50  | 30               | MHz   |
| $t_{PHL}, t_{PLH}$ | Maximum Propagation Delay, Clock to Output |            | 18  | 27               | ns    |
| $t_{PLH}$          | Maximum Propagation Delay, Clear to Output |            | 18  | 27               | ns    |
| $t_{REM}$          | Minimum Removal Time, Clear to Clock       |            | 10  | 20               | ns    |
| $t_s$              | Minimum Setup Time Data to Clock           |            | 10  | 20               | ns    |
| $t_H$              | Minimum Hold Time Clock to Data            |            | -2  | 0                | ns    |
| $t_w$              | Minimum Pulse Width Clock or Clear         |            | 10  | 16               | ns    |

**AC Electrical Characteristics**  $C_L=50\text{ pF}$ ,  $t_r=t_f=6\text{ ns}$  (unless otherwise specified)


| Symbol             | Parameter                                  | Conditions      | $V_{CC}$             | $T_A=25^\circ C$ |                    | $74HC$             | $54HC$             | Units             |
|--------------------|--|-----------------|----------------------|------------------|--------------------|--------------------|--------------------|-------------------|
|                    |  |                 |                      | Typ              | Guaranteed Limits  |                    |                    |                   |
| $f_{MAX}$          | Maximum Operating Frequency                |                 | 2.0V<br>4.5V<br>6.0V | 16<br>74<br>78   | 5<br>27<br>31      | 4<br>21<br>24      | 3<br>18<br>20      | MHz<br>MHz<br>MHz |
| $t_{PHL}, t_{PLH}$ | Maximum Propagation Delay, Clock to Output |                 | 2.0V<br>4.5V<br>6.0V | 38<br>14<br>12   | 135<br>27<br>23    | 170<br>34<br>29    | 205<br>41<br>35    | ns<br>ns<br>ns    |
| $t_{PLH}$          | Maximum Propagation Delay, Clear to Output |                 | 2.0V<br>4.5V<br>6.0V | 42<br>19<br>18   | 135<br>27<br>23    | 170<br>34<br>29    | 205<br>41<br>35    | ns<br>ns<br>ns    |
| $t_{REM}$          | Minimum Removal Time Clear to Clock        |                 | 2.0V<br>4.5V<br>6.0V | 0<br>0<br>0      | 25<br>5<br>4       | 32<br>6<br>5       | 37<br>7<br>6       | ns<br>ns<br>ns    |
| $t_s$              | Minimum Setup Time Data to Clock           |                 | 2.0V<br>4.5V<br>6.0V | 26<br>7<br>5     | 100<br>20<br>17    | 125<br>25<br>21    | 150<br>30<br>25    | ns<br>ns<br>ns    |
| $t_H$              | Minimum Hold Time Clock to Data            |                 | 2.0V<br>4.5V<br>6.0V | -15<br>-6<br>-4  | 0<br>0<br>0        | 0<br>0<br>0        | 0<br>0<br>0        | ns<br>ns<br>ns    |
| $t_w$              | Minimum Pulse Width Clock or Clear         |                 | 2.0V<br>4.5V<br>6.0V | 34<br>11<br>10   | 80<br>16<br>14     | 100<br>20<br>18    | 120<br>24<br>20    | ns<br>ns<br>ns    |
| $t_r, t_f$         | Maximum Input Rise and Fall Time, Clock    |                 | 2.0V<br>4.5V<br>6.0V |                  | 1000<br>500<br>400 | 1000<br>500<br>400 | 1000<br>500<br>400 | ns<br>ns<br>ns    |
| $t_{THL}, t_{TLH}$ | Maximum Output Rise and Fall Time          |                 | 2.0V<br>4.5V<br>6.0V | 28<br>11<br>9    | 75<br>15<br>13     | 95<br>19<br>16     | 110<br>22<br>19    | ns<br>ns<br>ns    |
| $C_{PD}$           | Power Dissipation Capacitance (Note 5)     | (per flip-flop) |                      | 45               |                    |                    |                    | pF                |
| $C_{IN}$           | Maximum Input Capacitance                  |                 |                      | 7                | 10                 | 10                 | 10                 | pF                |

Note 5:  $C_{PD}$  determines the no load dynamic power consumption,  $P_D=C_{PD} V_{CC}^2 f + I_{CC} V_{CC}$ , and the no load dynamic current consumption,  $I_S=C_{PD} V_{CC} f + I_{CC}$ .

3

## Logic Diagram

T-46-07-11



TL/F/5331-2