


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
FERRULE	BRASS	NICKEL
CENTER PIN	BRASS	GOLD
INSULATOR	ACETAL	WHITE


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	ECN 3165: UPDATE DWG FORMAT	01/21/2008	D.GRIFFIN
E	ECN 99999: OHMS WAS OHMT	04/12/2010	D.CASTRO
F	ECN 7510: UPDATED FORMAT, PKG, ROHS	07/14/2014	D.DESJARDIN
G	ECN 12137: REVISED RG59 TO RG58B/U, REVISED FORMAT AND ROHS STAMP	10/25/2022	SRautus




FERRULE




CENTER PIN



RECOMMENDED
FERRULE CRIMP SIZE



RECOMMENDED
PIN CRIMP SIZE



RECOMMENDED
CABLE STRIPPING



NOTES:

ELECTRICAL:
IMPEDANCE: 75 OHMS.

PACKAGING:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

APPLICATION:
RG59B/U & RG62 CABLE ASSEMBLIES

REGULATORY COMPLIANCE:
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY C.MCCORMICK	11/06/2001				
	CHECKED BY D.PARHAM	11/06/2001	CATEGORY AUDIO/VIDEO			
	APPROVED BY	11/06/2001				
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CONN BNC M RA RG59/62 CRIMP			
	COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. BAC706	REV. G
			SCALE: NONE CAD FILE: BAC706.SLDDRW			SHEET 1 OF 1