







RoHS



孔位 poles	A	B	孔位 poles	A	B
2	0	6.6	14	18.0	24.6
4	3.0	9.6	16	21.0	27.6
6	6.0	12.6	18	24.0	30.6
8	9.0	15.6	20	27.0	33.6
10	12.0	18.6	22	30.0	36.6
12	15.0	21.6	24	33.0	39.6

X.±0.50	X.°±
.X±0.25	.X°±
.XX± 0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF XFCN
AND SHALL NOT BE REPRODUCED,
COPIED OR CUED IN ANY MANNER
WITHOUT THE PRIOR WRITTEN CONSENT
OF XFCN

PART NO.: M3025RS-2xXX-BK		XFCN 兴飞连接器			
TITLE: 3.00mm Crimp Style Connectors		0769-82001899			
		www.xfconn.com			
APPD:		DWG NO: /			
CHKD:					
DRAW: Tong.Deng 2023.09.11			SCALE	SHEET	REV.
			NONE	1/1	A1