








NOTES :

1.Specification:


- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Mechanical Life: 3000cycles minimum
- 5>.Electrical Life:2000cycles minimum

2. PLATING:


GOLD FLASH 1u"~2u" SOLDER TAIL,  
1u"~3u" GOLD PLATING ON THE CONTACT AREA,  
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. CONTACT RATING:

- 1.SWITCHING: 25mA at 24VDC
- 2.NON-SWITCHING: 100mA at 50VDC  
WITH 50u" NICKEL UNDERPLATING OVERALL.



[P.C.B.LAYOUT]



[Schematic]

| PART NO. | 凸柄 (T) | DE-01PT | DE-02PT | DE-03PT | DE-04PT | DE-05PT | DE-06PT | DE-07PT | DE-08PT | DE-010PT |
|----------|--------|---------|---------|---------|---------|---------|---------|---------|---------|----------|
| 盖子/黑色    | 短柄 (D) | DE-01PD | DE-02PD | DE-03PD | DE-04PD | DE-05PD | DE-06PD | DE-07PD | DE-08PD | DE-010PD |

| Number | Part Name        | Material     | Finished     |
|--------|------------------|--------------|--------------|
| ①      | Actuator         | UL94 V0      | White        |
| ②      | Cover            | UL94 V0      | Black        |
| ③      | Movable          | Copper Alloy | 1u"~3u" Gold |
| ④      | Terminal         | Brass        | 1u"~2u" Gold |
| ⑤      | Base             | UL94 V0      | Black        |
| ⑥      | Terminal Contact | Brass        | 1u"~3u" Gold |

UNLESS OTHERWISE  
SPECIFIED TOLERANCES

DECIMALS: ANGLES:  
X :±0.30 X :±2°  
X.X :±0.20 X.X :±1°  
X.XX :±0.10



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

| TITLE | BY DSPV DIP SERIES PITCH 2.54mm |
|-------|---------------------------------|
| DWN   | xiong                           |
| CHKD  | lee                             |
| APVD  | wang                            |

CUSTOMER COPY