




WGF13N50SE

Features:

- ☐ Low Intrinsic Capacitances
- ☐ Excellent Switching Characteristics
- ☐ Extended Safe Operating Area
- ☐ Unrivalled Gate Charge :Qg= 50nC (Typ.)
- ☐ BVDSS=500V,ID=13A
- ☐ $R_{DS(on)}$:0.50 Ω (Max) @VG=10V
- ☐ 100% Avalanche Tested

TO-220F



Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DSS}	Drain-Source Voltage	500	V
I_D	Drain Current	$T_j=25^\circ\text{C}$	A
		$T_j=100^\circ\text{C}$	
$V_{GS(TH)}$	Gate Threshold Voltage	± 30	V
E_{AS}	Single Pulse Avalanche Energy (note1)	500	mJ
I_{AR}	Avalanche Current (note2)	13	A
P_D	Power Dissipation ($T_j=25^\circ\text{C}$)	50	W
T_j	Junction Temperature(Max)	150	$^\circ\text{C}$
T_{stg}	Storage Temperature	-55~+150	$^\circ\text{C}$
TL	Maximum lead temperature for soldering purpose,1/8" from case for 5 seconds	300	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JC}$	Thermal Resistance,Junction to Case	-	2.50	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance,Junction to Ambient	-	62.5	$^\circ\text{C/W}$

Electrical Characteristics (Ta=25°C unless otherwise noted)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250μA, V _{GS} =0	500	-	-	V
ΔBVDSS/ΔT _J	Breakdown Voltage Temperature Coefficient	I _D =250μA ,Reference to 25℃	-	0.65	-	V/℃
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =500V, V _{GS} =0V	-	-	1	μA
		V _{DS} =400V, T _j =125℃			100	
I _{GSSF}	Gate-body leakage Current, Forward	V _{GS} =+30V, V _{DS} =0V	-	-	100	nA
I _{GSSR}	Gate-body leakage Current, Reverse	V _{GS} =-30V, V _{DS} =0V	-	-	-100	
On Characteristics						
V _{GS(TH)}	Date Threshold Voltage	I _D =250μA,V _{DS} =V _{GS}	2	-	4	V
R _{DS(ON)}	Static Drain-Source On-Resistance	I _D =6.5A,V _{GS} =10V	-	0.45	0.50	Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =25V, V _{GS} =0, f=1.0MHz	-	1680	-	pF
C _{oss}	Output Capacitance		-	120	-	
C _{rss}	Reverse Transfer Capacitance		-	12	-	
Switching Characteristics						
T _{d(on)}	Turn-On Delay Time	V _{DD} =250V, I _D =13A R _G =25Ω (Note 3,4)	-	40	-	nS
Tr	Turn-On Rise Time		-	140	-	
T _{d(off)}	Turn-Off Delay Time		-	125	-	
T _f	Turn-Off Rise Time		-	85	-	
Q _g	Total Gate Charge	V _{DS} =400V,V _{GS} =10V, I _D =13A (Note 3,4)	-	50	-	nC
Q _{gs}	Gate-Source Charge		-	9.8	-	
Q _{gd}	Gate-Drain Charge		-	18.5	-	
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Max. Diode Forward Current	-	-	-	13	A
I _{SM}	Max. Pulsed Forward Current	-	-	-	52	
V _{SD}	Diode Forward Voltage	I _D =13A	-	-	1.4	V
T _{rr}	Reverse Recovery Time	I _S =13A,V _{GS} =0V diF/dt=100A/μs	-	420	-	nS
Q _{rr}	Reverse Recovery Charge	(Note3)	-	4.2	-	μC

Notes : 1, L=17.1mH, I_{AS}=13A, V_{DD}=50V, R_G=25Ω, Starting T_J=25°C

2, Repetitive Rating : Pulse width limited by maximum junction temperature

3, Pulse Test : Pulse Width ≤ 300μs, Duty Cycle ≤ 2%

4, Essentially Independent of Operating Temperature

Typical Characteristics



Fig1 Typical Output Characteristics, $T_C=25^\circ\text{C}$ 

Fig2 On-Resistance Vs. Drain Current and Gate Voltage




Fig3 Normalized On-Resistance Vs. Temperature




Fig4 Typical Source-Drain Diode Forward Voltage




Fig5 Maximum Drain Current Vs. Case Temperature






Fig6 Maximum Safe Operating Area


Gate Charge Test Circuit & Waveform




Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching Test Circuit & Waveforms




Peak Diode Recovery dv/dt Test Circuit & Waveforms



Package Dimension

TO-220F

Unit: mm



Symbol	Size		Symbol	Size		Symbol	Size		Symbol	Size	
	Min	Max		Min	Max		Min	Max		Min	Max
W	9.96	10.36	W4	0.25	0.45	L3	12.78	13.18	T3	0.45	0.60
W1	2.54 (TYP)		L	15.67	16.07	T	4.50	4.90	G(ϕ)	3.08	3.28
W2	0.70	0.90	L1	6.48	6.88	T1	2.34	2.74			
W3	1.24	1.47	L2	3.20	3.40	T2	2.56	2.96			