





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECO-17-011181	04AUG2017	RS	MZ
	P	REVISED PER ECO-18-000443	11JAN2018	RS	MZ
	R	REVISED PER ECO-20-001562	04FEB2020	SG	MZ



RECOMMENDED PC BOARD LAYOUT



- 1

HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- 2

BRASS PER ASTM B36.
- 3

3.81µm [.000150] MIN TIN-LEAD OVER 2.54µm [.000100] MIN COPPER OR 1.27µm [.000050] MIN NICKEL.
- 4

0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5


.000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN NICKEL.
- 6

0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END 3.81µm [.000150] MIN TIN FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 7

PRELIMINARY PART NUMBER.
- 8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

8	OBSOLETE	3.50 [.137]	6	1-207365-0
	OBSOLETE	7.52 [.296]	6	-207365-9-
		4.72 [.186]	6	207365-8
		4.72 [.186]	5	207365-7
	OBSOLETE	7.52 [.296]	4	-207365-6-
	OBSOLETE	4.72 [.186]	4	207365-3
	OBSOLETE	4.72 [.186]	3	207365-1
		A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 07/20/92		 TE Connectivity Ltd.								
DIMENSIONS: mm [INCHES]		CHK R.STONE 7-24-92										
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.TRAVIS 7-24-92		NAME PIN HEADER ASSEMBLY, 3 POSN, IN-LINE, SMALL METRIC CONNECTOR, METRIMATE							
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC —									
	MATERIAL		APPLICATION SPEC —						SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	HOUSING:  CONTACTS: 		FINISH CONTACTS: SEE TABLE						WEIGHT —	A2	00779	C-207365
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 1		REV R				