



SPECIFICATION FOR APPROVAL

产品规格承认书

Unibody Inductor

一体成型功率电感

CUSTOMER.

MODEL NO.

MS0650-6R8M

CUSTOMER'S PART NO.

LILE NO.

DATE.

2019-3-27

REVISION.

A/0

CUSTOMER APPROVE		
DATE:		
DRAWING		
DRAWN BY	CHECK BY	APPROVAL BY
DATE:		



sira
CERTIFICATION



IATF16949 / ISO9001 / ISO14000

深圳市迈翔科技有限公司


SHENZHEN MOTTO TECHNOLOGY Co., Ltd

香港瑞德科技有限公司 黄冈市迈翔电子有限公司

Motto Technology park, niu e ling village no#214 xintian,nghua Town,
Guanlan Street, Longhua District,Shenzhen

TEL: +86 0755-8948751~2 89487610 Fax: +86 0755-61624574

[Http://www.coilmx.com](http://www.coilmx.com) E-mail: sales@mottotech.com

CUSTOMER		MODEL NO.	MS0650-6R8M	REVISION	A/0
FILE NO.		PART NO.		DATE	2019-3-27
1.PRODUCT DIMENSION				UNIT:mm	
				A	7.15±0.35
				B	6.6±0.2
				C	5.0 Max
				D	3.0±0.5
				E	1.7±0.3
2.ELECTRICAL REQUIREMENTS					
PARAMETER	SPECIFICATION	CONDITION	TEST INSTRUMENTS		
L(uH)	6.8μH±20%	100KHz/1.0V	MICROTEST 6377		
DCR(mΩ)	40 mΩMAX	At 25℃	TH2512A		
I sat(A)	7.0A TYP L0A*70%	100KHz/1.0V	MICROTEST 6377+6220		
I rms(A)	5.5A TYP ΔT≤40℃	100KHz/1.0V	MICROTEST 6377+6220		
3.CHARACTERISTICS					
(1). All test data is based on 25℃ ambient.					
(2). DC current(A)that will cause an approximate ΔT40℃					
(3). DC current(A)that will cause L0 to drop approximately 30%Typ					
(4). Operating temperature range: -55℃~+125℃					
(5).The part temperature (ambient + temp rise)should not exceed 125℃ under worst case operating conditions. circuit design, component.PWB trace size and thickness,airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the den application					
4.SPECIAL REQUEST					
(1)Lettering 6R8 on top of the body.					

CUSTOMER		MODEL NO.	MS0650-6R8M	REVISION	A/0
FILE NO.		PART NO.		DATE	2019-3-27

5.PRODUCT IDENTIFICATION


XX XXXX - XXX X X

① ② ③ ④ ⑤

①、 Product Symbol ②、 Dimensions ③、 Inductance

④、 Tolerance: M±20%, N±30%. ⑤、 Material

6.ELECTRICAL SCHEMATICS




7.APPLICATION

- (1)Low profile,high current power supplies.
- (2)Battery powered devices.
- (3)DC/DC converters in distributed power systems.
- (5)DC/DC converters for field programmable gate array.


8.FEATURES


- (1)ROHS compliant.
- (2)Super low resistance,ultra high current rating.
- (3)high performance(I sat)realized by metal dust core.
- (4)Frequency Range:up to 1MHZ.

9.RECOMMENDED PCB LAYOUT



H	3.5
S	3.7
M	8.4

CUSTOMER		MODEL NO.		MS0650-6R8M		REVISION		A/0	
FILE NO.		PART NO.				DATE		2019-3-27	
SORT	ITEM	A	B	C	D	E			
PRODUCT & DIMENSION	SPEC	7.15±0.35	6.6±0.2	5.0 Max	3.0±0.5	1.7±0.3			
	1	7.18	6.65	4.87	2.92	1.74			
	2	7.22	6.65	4.92	2.93	1.75			
	3	7.21	6.64	4.88	2.92	1.74			
	4	7.20	6.65	4.91	2.92	1.74			
	5	7.19	6.64	4.92	2.92	1.75			
	X	7.20	6.65	4.90	2.92	1.74			
	R	0.04	0.01	0.05	0.01	0.01			
ELECTRICAL & REQUIREMENTS	ITEM	L(μH)	DCR (mΩ)	I sat(A)	DC BIAS	I rms	SHAPE:		
	SPEC	6.8μH±20%	40 mΩMAX	7.0A TYP L0A*70%		5.5A TYP ΔT≤40℃			
	1	6.783	34.820	5.012	-26.1%	OK			
	2	6.654	34.660	5.014	-24.6%	OK			
	3	6.589	34.260	5.011	-23.9%	OK			
	4	6.621	34.710	5.013	-24.3%	OK			
	5	6.783	35.050	5.019	-26.0%	OK			
	X	6.69	34.70	5.01	-25.0%				
	R	0.19	0.79	0.01	2.2%				



I(A)	0	1.4	2.8	4.2	5.6	7	8.4	9.8	
L(μH)	6.783	6.544	6.281	5.966	5.533	5.012	4.643	4.215	
ΔT(°C)	0	4.2	11.6	21.8	35.8	55.6	82.3		


CUSTOMER		MODEL NO.	MS0650-6R8M	REVISION	A/0
FILE NO.		PART NO.		DATE	2019-3-27
11.可靠性Reliability					
项目Item	规格与需求 Specification and Requirement		测试方法Test Method		
可焊性 Solder ability test	沾锡面积不得小于95%上锡面 Terminals area must have 95% min solder coverage		上锡升温曲线Solder heat proof: (1) 预热: 160±10℃持续90s Preheating: 160±10℃ for 90 seconds (2) 恒温时段: 245±5℃持续2±0.5s Retention time: 245±5℃ for 2±0.5 seconds		
振动测试 Vibration test	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1) 振动频率(10Hz 55Hz 10Hz)60s为一个周期 Vibration frequency: (10Hz to 55Hz to 10Hz) in 60 seconds as a period (2) 振动时间 Vibration time: 三维正交坐标系每个方向振动(周期) 循环2小时 Period cycled for 2 hours in each of 3 mutual perpendicular directions (3) 振幅 Amplitude: 1.5 mm Max		
冲击测试 Shock test	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1) 最大振幅 Peak value: 100G (2) 脉冲波长 Duration of pulse: 11ms (3) 三维正交坐标系每个方向正负方向冲击3次 Times in each positive and negative direction of 3 mutual perpendicular directions		
冷热冲击 Thermal shock	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1)重复以上100个循环Repeat 100 cycle as follow (-55±2℃,30±3分钟) 室温5分钟 (-55±2℃,30±3 minutes) Room temperature,5 minutes (+125±2℃,30±3分钟) 室温5分钟 (+125±2℃,30±3 minutes) Room temperature,5 minutes (2)恢复: 测试于标准条件下恢复48+4/-0小时 (参考注释1) Recovery:48+4/-0 hours of recovery under the standard condition after the test. (see Note1)		
耐高温测试 High temperature life test	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1)环境条件: 85±2℃ Environment condition : 85±2℃ 应用电流: 额定电流 Applied current: Rated current (2)持续时间: 1000+4/-0 小时 (参考注释1) Duration:1000+4/-0 hours (see Note1)		
耐湿测试 Humidity Resistance	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1)环境条件: 60±2℃ Environment condition : 60±2℃ 湿度: 90~95% Humidity:90~95% 应用电流: 额定电流 Applied current: Rated current (2)持续时间: 1000+4/-0 小时 (参考注释1) Duration:1000+4/-0 hours (see Note1)		
低温存放测试Low temperature life test	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1)存储温度 Store temperature -55±2℃下存放 1000+4/-0 小时 -55±2℃ for total 1000+4/-0 hours		
高温存放测试High temperature life test	感值变化: 不超过±5% 且无破裂等机械损伤产生 Inductance change: Within±5% Without mechanical damage such as break		(1)存储温度 Store temperature +125±2℃下存放 1000+4/-0 小时 +125±2℃ for total 1000+4/-0 hours		

CUSTOMER		MODEL NO.	MS0650-6R8M	REVISION	A/0
FILE NO.		PART NO.		DATE	2019-3-27

12、包装 Packaging


12.1、尺寸 Dimensions

12.1.1 包装料带尺寸 Tape packaging dimensions




W	A0	B0	K0	P	F	E	D0	P0	T
16.00 ±0.30	7.05 ±0.10	7.2 ±0.10	5.3 ±0.10	12 ±0.10	11.5 ±0.1	1.75 ±0.10	1.50 ±0.10	4.0 ±0.10	0.35 ±0.05

12.1.2 卷轴尺寸 Reel dimensions



项目	尺寸(mm)
A	330.0 ± 2.0
B	100.0 ± 1.0
C	13.0 ± 1.0
D	1.9 ± 0.4
W	30.4 Max
W1	24.4 ± 1.0

12.1.3 外箱尺寸Carton dimensions



项目	数量(PCS)
1卷轴	1000
1内箱	3000
1外箱	9000

CUSTOMER

MODEL NO.

MS0650-6R8M

REVISION

A/0

FILE NO.

PART NO.


DATE

2019-3-27

Reflow curve

※ Reflow Profile

Power Choke Coil Type



1. Reflow Soldering Method

Reflow Soldering	T_p :255~260°C	Max.30 seconds (tp)
	217°C	60~150 seconds
Pre-Heat	150 ~ 200°C	60~120 seconds
Time 25°C to peak temperature	8 minutes max.	

2. Soldering iron method : 350±5°C Max.3 seconds.