## ADVANCE INFORMATION

All information in this data sheet is preliminary and subject to change.



## 2A, Current-Limited, High-Side P-Channel Switch with Thermal Shutdown

#### General Description

The MAX869L P-channel load switch features an accurate user-set current limit and low on-resistance. This switch is designed to protect your power source from shorts and surges by limiting current and preventing the system supply from being pulled low. The input voltage range is 2.7V to 5.5V.

The MAX869L features a 2A,  $45m\Omega$  switch controlled by a logic signal. Current-limit accuracy is ±21%, and can be set from 400mA to 2.4A using a single resistor.

The device has a low 12µA quiescent supply current. which reduces to 2µA max in shutdown. It features thermal-shutdown protection and a logic-signal output pin (FAULT) that signals when there is an overcurrent or overtemperature condition.

For other devices in this family, consult the Selector Guide.

#### Features

- Very Small Footprint (16-pin QSOP is the same size as an 8-pin SO)
- Low Resistance: 45mΩ at 3V
- ♦ ±21%-Accurate, User-Set Current Limit.
- ↑ 12µA (typ) Quiescent Current
- ◆ 0.01µA (tvp) Shutdown Current
- ◆ 0.04µA (typ) Leakage to Output when Switch
- ♦ 2.7V to 5.5V Input Range
- ♦ Thermal Shutdown
- **◆ FAULT** Output

#### Selector Guide

PART	R <sub>ON</sub> AT 3V (mΩ)	NOMINAL CURRENT (A)	COUNT	PACKAGE
MAX869L	45	2	Single	16 QSOP
MAX890L	90	1	Single	8 SO
MAX891L	150	0.5	Single	8 µMAX
MAX892L	300	0.25	Single	8 µMAX
MAX894L	150	0.5	Dual	8 SO
MAX895L	300	0.25	Dual	8 SO

## **Applications**

Universal Serial Bus (USB)

Notebook Computers

Personal Communicators

Palmtop Computers

Hand-Held Instruments


Portable Medical Instruments

## Ordering Information

PART	TEMP. RANGE	PIN-PACKAGE
MAX869LC/D	0°C to +70°C	Dice*
MAX869LEEE	-40°C to +85°C	16 QSOP

<sup>\*</sup>Dice are specified at TA = +25°C.

## Typical Operating Circuit



MIXLM

Maxim integrated Products 4-75

# 2A, Current-Limited, High-Side P-Channel Switch with Thermal Shutdown

