Ratings Voltage: 300 V Temperature: -80~200 °C Flammability: VW-1 Oil resistance: 60 °C

≥50% elongation and tensile strength after aging

Conductor

Conductor count: 1
Gauge: 18 AWG 0.82 mm²
Material: tinned copper strands
Strand size: Ø0.235 mm x 19
Resistance at 20 °C: 23.2 Ω /km max

Material: Fluorinated ethylene propylene (FEP) Color: red


Diameter: \emptyset 1.8 \pm 0.1 Nominal thickness: 0.33 mm Resistance at 20 °C: 2.5 M Ω /kft min

Wire marking: E339579 UL AWM STYLE 1332 18AWG 200°C 300V VW-1 - - - cUL AWM I A/B 200°C 300V FT1 TENSILITY

Mechanical Tests

After aging at 232±1°C for 7 days
Minimum tensile strength 1.76 kgf/mm²
Minimum elongation 200% original

5



Revis	on: Date:	Description:	Prepared:	Notes: RoHS compliant Function test: no open, no short circuit, no Intermittent						custom
Α	05/25/2022	Initial release				TENSILITY				
			Verified:			1 541 222 2220 077 670 7110				see a cı
			Dimensions are in							0.5
			millimeters. Tolerances:	Description: Wire, hook-up, TS, 18 AWG, UL 1332, 300V, 200C, 1.8 mm, FEP, red		Size: Part number:				-
			X: ± 0.5 mm			Α	30-02541			
			X.X: ± 0.3 mm X.XX: ± 0.05 mm			Scale:	25:1		Sheet 1 of 1	

email engineering@tensility.com version of this cable assembly, call Tensility at 541-323-3228 or

3 2