MAXIM

Dual 1:5 Differential LVPECL/LVECL/HSTL Clock and Data Drivers

MAX9312/MAX9314

General Description

The MAX9312/MAX9314 are low skew, dual 1-to-5 differential drivers designed for clock and data distribution. These devices accept two inputs. Each input is reproduced at five differential outputs. The differential inputs can be adapted to accept single-ended inputs by connecting the on-chip V$_{BB}$ supply to one input as a reference voltage.

The MAX9312/MAX9314 feature low part-to-part skew (30ps) and output-to-output skew (12ps), making them ideal for clock and data distribution across a backplane or a board. For interfacing to differential HSTL and LVPECL signals, these devices operate over a +2.25V to +3.8V supply range, allowing high-performance clock or data distribution in systems with a nominal +2.5V or +3.3V supply. For differential LVECL operation, these devices operate from a -2.25V to -3.8V supply.

The MAX9312 features an on-chip V$_{BB}$ reference output of 1.425V below the positive supply voltage. The MAX9314 offers an on-chip V$_{BB}$ reference output of 1.32V below the positive supply voltage.

Both devices are offered in space-saving, 32-pin 5mm × 5mm TQFP, 5mm x 5mm QFN, and industry-standard 32-pin 7mm × 7mm TQFP packages.

Applications

Precision Clock Distribution

Low-Jitter Data Repeater

Features

♦ **+2.25V to +3.8V Differential HSTL/LVPECL Operation**

♦ **-2.25V to -3.8V Differential LVECL Operation**

♦ **30ps (typ) Part-to-Part Skew**

♦ **12ps (typ) Output-to-Output Skew**

♦ **312ps (typ) Propagation Delay**

♦ **≥ 300mV Differential Output at 3GHz**

♦ **On-Chip Reference for Single-Ended Inputs**

♦ **Output Low with Open Input**

♦ **Pin Compatible with MC100LVEP210 (MAX9312) and MC100EP210 (MAX9314)**

♦ **Offered in Tiny QFN* Package (70% Smaller Footprint than LQFP)**

Ordering Information

PART	TEMP. RANGE	PIN-PACKAGE
MAX9312ECJ	-40°C to +85°C	32 TQFP (7mm × 7mm)
MAX9312EGJ*	-40°C to +85°C	32 QFN (5mm × 5mm)
MAX9312EHJ*	-40°C to +85°C	32 TQFP (5mm × 5mm)
MAX9314ECJ	-40°C to +85°C	32 TQFP (7mm × 7mm)
MAX9314EGJ*	-40°C to +85°C	32 QFN (5mm × 5mm)
MAX9314EHJ*	-40°C to +85°C	32 TQFP (5mm × 5mm)

*Future product—contact factory for availability.

Functional Diagram

Pin Configuration appears at end of data sheet.

MAXIM

_____ **Maxim Integrated Products** 1

For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

Dual 1:5 Differential LVPECL/LVECL/HSTL Clock and Data Drivers

ABSOLUTE MAXIMUM RATINGS

V_{CC} - V_{EE}...4.1V
Inputs (CLK_, $\overline{CLK\_}$)............................V_{EE} - 0.3V to V_{CC} + 0.3V
CLK_ to $\overline{CLK\_}$ ....±3.0V
Continuous Output Current...50mA
Surge Output Current...100mA
V_{BB} Sink/Source Current ....±0.65mA
Junction-to-Ambient Thermal Resistance in Still Air
   32-Pin 7mm × 7mm TQFP...+90°C/W
Junction-to-Ambient Thermal Resistance with
500 LFPM Airflow
   32-Pin 7mm × 7mm TQFP...+60°C/W

Junction-to-Case Thermal Resistance
   32-Pin 7mm × 7mm TQFP...+12°C/W
Operating Temperature Range ....-40°C to +85°C
Junction Temperature..+150°C
Storage Temperature Range ....-65°C to +150°C
ESD Protection
   Human Body Model (CLK_, $\overline{CLK\_}$, Q_, $\overline{Q\_}$) 2kV
Soldering Temperature (10s)...+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

(V_{CC} - V_{EE} = +2.25V to +3.8V, outputs loaded with 50Ω ±1% to V_{CC} - 2V.) (Notes 1–4)

PARAMETER	SYMBOL	CONDITIONS		-40°C		+25°C		+85°C		UNITS
				MIN	MAX	MIN	MAX	MIN	MAX	
INPUTS (CLK_, $\overline{CLK\_}$)										
Single-Ended Input High Voltage	V_{IH}	V_{BB} connected to $\overline{CLK\_}$ (V_{IL} for V_{BB} connected to CLK_)	MAX9312	V_{CC} - 1.23	V_{CC}	V_{CC} - 1.23	V_{CC}	V_{CC} - 1.23	V_{CC}	V
			MAX9314	V_{CC} - 1.165	V_{CC}	V_{CC} - 1.165	V_{CC}	V_{CC} - 1.165	V_{CC}	
Single-Ended Input Low Voltage	V_{IL}	V_{BB} connected to $\overline{CLK\_}$ (V_{IL} for V_{BB} connected to CLK_)	MAX9312	V_{EE}	V_{CC} - 1.62	V_{EE}	V_{CC} - 1.62	V_{EE}	V_{CC} - 1.62	V
			MAX9314	V_{EE}	V_{CC} - 1.475	V_{EE}	V_{CC} - 1.475	V_{EE}	V_{CC} - 1.475	
High Voltage of Differential Input	V_{IHD}			V_{EE} + 1.2	V_{CC}	V_{EE} + 1.2	V_{CC}	V_{EE} + 1.2	V_{CC}	V
Low Voltage of Differential Input	V_{ILD}			V_{EE}	V_{CC} - 0.095	V_{EE}	V_{CC} - 0.095	V_{EE}	V_{CC} - 0.095	V
Differential Input Voltage	V_{IHD} - V_{ILD}	For V_{CC} - V_{EE} < 3.0V		0.095	V_{CC} - V_{EE}	0.095	V_{CC} - V_{EE}	0.095	V_{CC} - V_{EE}	V
		For V_{CC} - V_{EE} ≥ 3.0V		0.095	3.0	0.095	3.0	0.095	3.0	
Input High Current	I_{IH}				150		150		150	µA
CLK_ Input Low Current	I_{ILCLK}			-10	+10	-10	+10	-10	+10	µA

MAXIM

DC ELECTRICAL CHARACTERISTICS (continued)

(V_{CC} - V_{EE} = +2.25V to +3.8V, outputs loaded with 50Ω ±1% to V_{CC} - 2V.) (Notes 1–4)

PARAMETER	SYMBOL	CONDITIONS		-40°C MIN	-40°C MAX	+25°C MIN	+25°C MAX	+85°C MIN	+85°C MAX	UNITS
$\overline{CLK}$_ Input Low Current	$I_{IL\overline{CLK}}$			-150		-150		-150		µA
OUTPUTS (Q__, $\overline{Q}$__)										
Single-Ended Output High Voltage	V_{OH}	Figure 1		V_{CC} - 1.025	V_{CC} - 0.900	V_{CC} - 1.025	V_{CC} - 0.900	V_{CC} - 1.025	V_{CC} - 0.900	V
Single-Ended Output Low Voltage	V_{OL}	Figure 1		V_{CC} - -1.930	V_{CC} - 1.695	V_{CC} - -1.930	V_{CC} - 1.695	V_{CC} - -1.930	V_{CC} - 1.695	V
Differential Output Voltage	V_{OH} - V_{OL}	Figure 1		670	950	670	950	670	950	mV
REFERENCE (V_{BB})										
Reference Voltage Output (Note 5)	V_{BB}	I_{BB} = ±0.5mA	MAX9312	V_{CC} - 1.525	V_{CC} - 1.325	V_{CC} - 1.525	V_{CC} - 1.325	V_{CC} - 1.525	V_{CC} - 1.325	V
			MAX9314	V_{CC} - 1.38	V_{CC} - 1.26	V_{CC} - 1.38	V_{CC} - 1.26	V_{CC} - 1.38	V_{CC} - 1.26	
POWER SUPPLY										
Supply Current (Note 6)	I_{EE}				75		82		95	mA

MAX9312/MAX9314

AC ELECTRICAL CHARACTERISTICS

(V_{CC} - V_{EE} = +2.25V to +3.8V, outputs loaded with 50Ω ±1% to V_{CC} - 2V, input frequency = 1.5GHz, input transition time = 125ps (20% to 80%), V_{IHD} = V_{EE} + 1.2V to V_{CC}, V_{ILD} = V_{EE} to V_{CC} - 0.15V, V_{IHD} - V_{ILD} = 0.15V to the smaller of 3V or V_{CC} - V_{EE}, unless otherwise noted. Typical values are at V_{CC} - V_{EE} = 3.3V, V_{IHD} = V_{CC} - 1V, V_{ILD} = V_{CC} - 1.5V.) (Note 7)

| PARAMETER	SYMBOL	CONDITIONS	-40°C MIN	-40°C TYP	-40°C MAX	+25°C MIN	+25°C TYP	+25°C MAX	+85°C MIN	+85°C TYP	+85°C MAX	UNITS
Differential Input-to-Output Delay	t_{PLHD}, t_{PHLD}	Figure 2	220	321	380	220	312	410	260	322	400	ps
Output-to-Output Skew (Note 8)	t_{SKOO}			12	46		12	46		10	35	ps
Part-to-Part Skew (Note 9)	t_{SKPP}			30	160		30	190		30	140	ps
Added Random Jitter (Note 10)	t_{RJ}	f_{IN} = 1.5GHz clock pattern		1.2	2.5		1.2	2.5		1.2	2.5	ps (RMS)
		f_{IN} = 3.0GHz clock pattern		1.2	2.6		1.2	2.6		1.2	2.6	
Added Deterministic Jitter (Note 10)	t_{DJ}	3Gbps, 2^{23} -1 PRBS pattern		80	95		80	95		80	95	ps (pk-pk)
Switching Frequency	f_{MAX}	V_{OH} - V_{OL} ≥ 300mV, clock pattern, Figure 2		3.0			3.0			3.0		GHz
		V_{OH} - V_{OL} ≥ 500mV, clock pattern, Figure 2	1.5			1.5			1.5			
Output Rise/Fall Time (20% to 80%)	t_R, t_F	Figure 2	100	112	140	100	116	140	100	121	140	ps

Note 1: Measurements are made with the device in thermal equilibrium.
Note 2: Current into a pin is defined as positive. Current out of a pin is defined as negative.
Note 3: Single-ended input operation using V_{BB} is limited to V_{CC} - V_{EE} = 3.0V to 3.8V for the MAX9312 and V_{CC} - V_{EE} = 2.7V to 3.8V for the MAX9314.
Note 4: DC parameters production tested at T_A = +25°C. Guaranteed by design and characterization over the full operating temperature range.
Note 5: Use V_{BB} only for inputs that are on the same device as the V_{BB} reference.
Note 6: All pins open except V_{CC} and V_{EE}.
Note 7: Guaranteed by design and characterization limits are set at ±6 sigma.
Note 8: Measured between outputs on the same part at the signal crossing points for a same-edge transition.
Note 9: Measured between outputs of different parts at the signal crossing points under identical conditions for a same-edge transition.
Note 10: Device jitter added to the input signal.

MAXIM

Typical Operating Characteristics

(V_{CC} = +3.3V, V_{EE} = 0, V_{IHD} = V_{CC} - 0.95V, V_{ILD} = V_{CL} - 1.25V, input transition time = 125ps (20% to 80%), f_{IN} = 1.5GHz, outputs loaded with 50Ω to V_{CC} - 2V, T_A = +25°C, unless otherwise noted.)

MAX9312/MAX9314

SUPPLY CURRENT, I_{EE} vs. TEMPERATURE

OUTPUT AMPLITUDE (V_{OH} - V_{OL}) vs. FREQUENCY

TRANSITION TIME vs. TEMPERATURE

PROPAGATION DELAY vs. SINGLE-ENDED HIGH VOLTAGE OF DIFFERENTIAL INPUT (V_{IHD})

PROPAGATION DELAY vs. TEMPERATURE

_____*Pin Description*

PIN	NAME	FUNCTION
1, 9, 16, 25, 32	V_{CC}	Positive Supply Voltage. Bypass from V_{CC} to V_{EE} with 0.1µF and 0.01µF ceramic capacitors. Place the capacitors as close to the device as possible with the smaller value capacitor closest to the device.
2	N.C.	Not Connected
3	CLKA	Noninverting Differential Clock Input A
4	$\overline{CLKA}$	Inverting Differential Clock Input A
5	V_{BB}	Reference Output Voltage. Connect to the inverting or noninverting clock input to provide a reference for single-ended operation. When used, bypass to V_{CC} with a 0.01µF ceramic capacitor.
6	CLKB	Noninverting Differential Clock Input B
7	$\overline{CLKB}$	Inverting Differential Clock Input B
8	V_{EE}	Negative Supply Voltage
10	$\overline{QB4}$	Inverting QB4 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
11	QB4	Noninverting QB4 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
12	$\overline{QB3}$	Inverting QB3 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
13	QB3	Noninverting QB3 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
14	$\overline{QB2}$	Inverting QB2 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
15	QB2	Noninverting QB2 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
17	$\overline{QB1}$	Inverting QB1 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
18	QB1	Noninverting QB1 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
19	$\overline{QB0}$	Inverting QB0 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
20	QB0	Noninverting QB0 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
21	$\overline{QA4}$	Inverting QA4 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
22	QA4	Noninverting QA4 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
23	$\overline{QA3}$	Inverting QA3 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
24	QA3	Noninverting QA3 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
26	$\overline{QA2}$	Inverting QA2 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
27	QA2	Noninverting QA2 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
28	$\overline{QA1}$	Inverting QA1 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
29	QA1	Noninverting QA1 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
30	$\overline{QA0}$	Inverting QA0 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.
31	QA0	Noninverting QA0 Output. Typically terminate with 50Ω resistor to V_{CC} - 2V.

MAXIM

Dual 1:5 Differential LVPECL/LVECL/HSTL Clock and Data Drivers

Detailed Description

The MAX9312/MAX9314 are low-skew, dual 1-to-5 differential drivers designed for clock and data distribution.

For interfacing to differential HSTL and LVPECL signals, these devices operate over a +2.25V to +3.8V supply range, allowing high-performance clock or data distribution in systems with a nominal +2.5V or +3.3V supply. For differential LVECL operation, these devices operate from a -2.25V to -3.8V supply.

The differential inputs can be configured to accept single-ended inputs when operating at approximately V_{CC} - V_{EE} = 3.0V to 3.8V for the MAX9312 or V_{CC} - V_{EE} = 2.7V to 3.8V for the MAX9314. This is accomplished by connecting the on-chip reference voltage, V_{BB}, to an input as a reference. For example, the differential CLKA, $\overline{CLKA}$ input is converted to a noninverting, single-ended input by connecting V_{BB} to $\overline{CLKA}$ and connecting the single-ended input to CLKA. Similarly, an inverting input is obtained by connecting V_{BB} to CLKA and connecting the single-ended input to $\overline{CLKA}$. With a differential input configured as single ended (using V_{BB}), the single-ended input can be driven to V_{CC} and V_{EE} or with a single-ended LVPECL/LVECL signal.

When a differential input is configured as a single-ended input (using V_{BB}), the approximate supply range is V_{CC} - V_{EE} = 3.0V to 3.8V for the MAX9312 and V_{CC} - V_{EE} = 2.7V to 3.8V for the MAX9314. This is because one of the inputs must be V_{EE} + 1.2V or higher for proper operation of the input stage. V_{BB} must be at least V_{EE} + 1.2V because it becomes the high-level input when the other (single-ended) input swings below it. Therefore, minimum V_{BB} = V_{EE} + 1.2V.

The minimum V_{BB} output for the MAX9312 is V_{CC} - 1.525V and the minimum V_{BB} output for the MAX9314 is V_{CC} - 1.38V. Substituting the minimum V_{BB} output for each device into V_{BB} = V_{EE} + 1.2V results in a minimum supply of 2.725V for the MAX9312 and 2.58V for the MAX9314. Rounding up to standard supplies gives the single-ended operating supply ranges of V_{CC} - V_{EE} = 3.0V to 3.8V for the MAX9312 and V_{CC} - V_{EE} = 2.7V to 3.8V for the MAX9314.

When using the V_{BB} reference output, bypass it with a 0.01µF ceramic capacitor to V_{CC}. If the V_{BB} reference is not used, it can be left open. The V_{BB} reference can source or sink 0.5mA, which is sufficient to drive two inputs. Use V_{BB} only for inputs that are on the same device as the V_{BB} reference.

The maximum magnitude of the differential input from CLK_ to $\overline{CLK\_}$ is 3.0V or V_{CC} - V_{EE}, whichever is less.

This limit also applies to the difference between any reference voltage input and a single-ended input.

The differential inputs have bias resistors that drive the outputs to a differential low when the inputs are open. The inverting inputs ($\overline{CLKA}$ and $\overline{CLKB}$) are biased with a 75kΩ pullup to V_{CC} and a 75kΩ pulldown to V_{EE}. The noninverting inputs (CLKA and CLKB) are biased with a 75kΩ pulldown to V_{EE}.

Specifications for the high and low voltages of a differential input (V_{IHD} and V_{ILD}) and the differential input voltage (V_{IHD} - V_{ILD}) apply simultaneously (V_{ILD} cannot be higher than V_{IHD}).

Output levels are referenced to V_{CC} and are considered LVPECL or LVECL, depending on the level of the V_{CC} supply. With V_{CC} connected to a positive supply and V_{EE} connected to GND, the outputs are LVPECL. The outputs are LVECL when V_{CC} is connected to GND and V_{EE} is connected to a negative supply.

A single-ended input of at least V_{BB} ±95mV or a differential input of at least 95mV switches the outputs to the V_{OH} and V_{OL} levels specified in the *DC Electrical Characteristics* table.

Applications Information

Supply Bypassing

Bypass V_{CC} to V_{EE} with high-frequency surface-mount ceramic 0.1µF and 0.01µF capacitors in parallel as close to the device as possible, with the 0.01µF value capacitor closest to the device. Use multiple parallel vias for low inductance. When using the V_{BB} reference output, bypass it with a 0.01µF ceramic capacitor to V_{CC} (if the V_{BB} reference is not used, it can be left open).

Traces

Input and output trace characteristics affect the performance of the MAX9312/MAX9314.

Connect each signal of a differential input or output to a 50Ω characteristic impedance trace. Minimize the number of vias to prevent impedance discontinuities. Reduce reflections by maintaining the 50Ω characteristic impedance through connectors and across cables. Reduce skew within a differential pair by matching the electrical length of the traces.

Output Termination

Terminate outputs through 50Ω to V_{CC} - 2V or use an equivalent Thevenin termination. When a single-ended signal is taken from a differential output, terminate both outputs. For example, if QA0 is used as a single-ended output, terminate both QA0 and $\overline{QA0}$.

MAX9312/MAX9314


Figure 1. Switching with Single-Ended Input

Figure 2. Differential Transition Time and Propagation Delay Timing Diagram

_____**Pin Configuration**

_____**Chip Information**

TRANSISTOR COUNT: 250

TOP VIEW

TQFP (7mm × 7mm), TQFP (5mm × 5mm),
QFN (NO LEADS EXTENDING FROM QFN PACKAGE)

MAXIM

MAX9312/MAX9314

TOP VIEW

FOR ODD TERMINAL/SIDE   FOR EVEN TERMINAL/SIDE

TERMINAL TIP

SECTION "C-C"
SCALE: NONE

SEATING PLANE

BOTTOM VIEW

/VI /IXI/VI
PROPRIETARY INFORMATION
TITLE:
PACKAGE OUTLINE, 16,20,28,32L QFN, 5x5x0.90 MM

APPROVAL	DOCUMENT CONTROL NO.	REV	
	21-0091	G	1/2

NOTES:

1. DIE THICKNESS ALLOWABLE IS 0.305mm MAXIMUM (.012 INCHES MAXIMUM)
2. DIMENSIONING & TOLERANCES CONFORM TO ASME Y14.5M. – 1994.
3. N IS THE NUMBER OF TERMINALS.
   Nd IS THE NUMBER OF TERMINALS IN X–DIRECTION &
   Ne IS THE NUMBER OF TERMINALS IN Y–DIRECTION.
4. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED
   BETWEEN 0.20 AND 0.25mm FROM TERMINAL TIP.
5. THE PIN #1 IDENTIFIER MUST BE EXISTED ON THE TOP SURFACE OF THE
   PACKAGE BY USING INDENTATION MARK OR INK/ LASER MARKED.
6. EXACT SHAPE AND SIZE OF THIS FEATURE IS OPTIONAL.
7. ALL DIMENSIONS ARE IN MILLIMETERS.
8. PACKAGE WARPAGE MAX 0.05mm.
9. APPLIED FOR EXPOSED PAD AND TERMINALS.
   EXCLUDE EMBEDDED PART OF EXPOSED PAD FROM MEASURING.
10. MEETS JEDEC MO220.
11. THIS PACKAGE OUTLINE APPLIES TO ANVIL SINGULATION (STEPPED SIDES)
    AND TO SAW SINGULATION (STRAIGHT SIDES) QFN STYLES.

SYMBOL	COMMON DIMENSIONS			NOTE
	MIN.	NOM.	MAX.	
A	0.80	0.90	1.00	
A1	0.00	0.01	0.05	
A2	0.00	0.65	1.00	
A3		0.20 REF.		
D		5.00 BSC		
D1		4.75 BSC		
E		5.00 BSC		
E1		4.75 BSC		
θ	0°	–	12°	
P	0		0.60	
D2	1.25	–	3.25	
E2	1.25	–	3.25	

SYMBOL	PITCH VARIATION B			NOTE	SYMBOL	PITCH VARIATION B			NOTE	SYMBOL	PITCH VARIATION C			NOTE	SYMBOL	PITCH VARIATION D			NOTE
	MIN.	NOM.	MAX.			MIN.	NOM.	MAX.			MIN.	NOM.	MAX.			MIN.	NOM.	MAX.	
e		0.80 BSC			e		0.65 BSC			e		0.50 BSC			e		0.50 BSC		
N		16		3	N		20		3	N		28		3	N		32		3
Nd		4		3	Nd		5		3	Nd		7		3	Nd		8		3
Ne		4		3	Ne		5		3	Ne		7		3	Ne		8		3
L	0.35	0.55	0.75		L	0.35	0.55	0.75		L	0.35	0.55	0.75		L	0.30	0.40	0.50	
b	0.28	0.33	0.40	4	b	0.23	0.28	0.35	4	b	0.18	0.23	0.30	4	b	0.18	0.23	0.30	4

/VI /IXI/VI
PROPRIETARY INFORMATION
TITLE:
PACKAGE OUTLINE, 16,20,28,32L QFN, 5x5x0.90 MM

APPROVAL	DOCUMENT CONTROL NO.	REV	
	21-0091	G	2/2

/VI/IXI/VI

MAX9312/MAX9314

NOTES:
1. ALL DIMENSIONING AND TOLERANCING CONFORM TO ANSI Y14.5-1982.
2. DATUM PLANE ⊞ IS LOCATED AT MOLD PARTING LINE AND COINCIDENT WITH LEAD, WHERE LEAD EXITS PLASTIC BODY AT BOTTOM OF PARTING LINE.
3. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE MOLD PROTRUSION IS 0.254 MM ON D1 AND E1 DIMENSIONS.
4. THE TOP OF PACKAGE IS SMALLER THAN THE BOTTOM OF PACKAGE BY 0.15 MILLIMETERS.
5. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 MM TOTAL IN EXCESS OF THE b DIMENSION AT MAXIMUM MATERIAL CONDITION.
6. CONTROLLING DIMENSION: MILLIMETER.
7. THIS OUTLINE CONFORMS TO JEDEC PUBLICATION 95, REGISTRATION MO-136.
8. LEADS SHALL BE COPLANAR WITHIN .004 INCH.

JEDEC VARIATIONS		
DIMENSIONS IN MILLIMETERS		
AA		
5x5x1.0 MM		
	MIN.	MAX.
A	—	1.20
A₁	0.05	0.15
A₂	0.95	1.05
D	7.00 BSC.	
D₁	5.00 BSC.	
E	7.00 BSC.	
E₁	5.00 BSC.	
L	0.45	0.75
M	0.15	—
N	32	
e	0.50 BSC.	
b	0.17	0.27
b1	0.17	0.23

MAXIM
PROPRIETARY INFORMATION
TITLE:
PACKAGE OUTLINE, 32L TQFP, 5x5x1.0 MM
APPROVAL | DOCUMENT CONTROL NO. 21-0110 | REV A | 2/2

MAXIM

Package Information (continued)

JEDEC VARIATION

	BC 32 LEAD		BE 48 LEAD	
	MIN.	MAX.	MIN.	MAX.
A	---	1.60	---	1.60
A1	0.05	0.15	0.05	0.15
A2	1.35	1.45	1.35	1.45
D	8.90	9.10	8.90	9.10
D1	7.00 BSC.		7.00 BSC.	
E	8.90	9.10	8.90	9.10
E1	7.00 BSC.		7.00 BSC.	
e	0.8 BSC.		0.5 BSC.	
L	0.45	0.75	0.45	0.75
b	0.30	0.45	0.17	0.27
c	0.09	0.20	0.09	0.20
α	0°	7°	0°	7°

NOTES:
1. ALL DIMENSIONING AND TOLERANCING CONFORM TO ANSI Y14.5-1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. THIS OUTLINE CONFORMS TO JEDEC PUBLICATION 95 REGISTRATION MO-136, VARIATIONS BC AND BE.
4. LEADS SHALL BE COPLANAR WITHIN .004 INCH.

MAXIM

PROPRIETARY INFORMATION

TITLE: PACKAGE OUTLINE, 32/48L, 7x7x1.4 MM TQFP

APPROVAL

DOCUMENT CONTROL NO. 21-0054

REV D

1/1

32L/48L.TQFP.EPS

MAX9312/MAX9314

Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600 _____ 11