

Features

- High Blocking Voltage with Low On-Resistance
- High Speed Switching with Low Capacitances
- Easy to Parallel and Simple to Drive
- Avalanche Ruggedness
- Halogen Free, RoHS Compliant



Benefits

- Higher System Efficiency
- Reduced Cooling Requirements
- Increased Power Density
- Increased System Switching Frequency

Applications

- Solar Inverters
- Switch Mode Power Supplies
- High Voltage DC/DC Converters
- Battery Chargers
- Motor Drives
- Pulsed Power applications

Package



Maximum Ratings ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
$V_{DS\max}$	Drain - Source Voltage	650	V	$V_{GS}=0\text{V}, I_D=100\mu\text{A}$	
$V_{GS\max}$	Gate - Source Voltage	-8/+22	V	Absolute maximum values	
V_{GSop}	Gate - Source Voltage	-5/+18	V	Recommended operational values	
I_D	Continuous Drain Current	40 29	A	$V_{GS}=20\text{V}, T_c=25^\circ\text{C}$ $V_{GS}=20\text{V}, T_c=100^\circ\text{C}$	
I_{DM}	Pulse Drain Current	90	A	Pulse width limited by $T_{j\max}$	
P_D	Power Dissipation	150	W	$T_c=25^\circ\text{C}, T_j=175^\circ\text{C}$	Fig. 11
T_j, T_{stg}	Operating Junction and Storage Temperature	-55 to +175	°C		

Electrical Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
V _{(BR)DSS}	Drain-Source Breakdown Voltage	650			V	V _{GS} =0V, I _D =100µA	
V _{GS(th)}	Gate Threshold Voltage	2.0	3.2	4.0	V	V _{GS} = V _{DS} , I _D =5mA, T _C =25°C	Fig. 6
			2.3			V _{GS} = V _{DS} , I _D =5mA, T _C =175°C	
I _{DSS}	Zero Gate Voltage Drain Current		1	100	µA	V _{DS} = 650V, V _{GS} =0V	
I _{GSS}	Gate-Source Leakage Current		50	200	nA	V _{GS} =18V, V _{DS} = 0V	
R _{D(on)}	Drain-Source on-state Resistance		45	65	mΩ	V _{GS} = 18 V, I _D =20A, T _C =25°C	Fig. 4
			75			V _{GS} = 18 V, I _D =20A, T _C =175°C	
g _{fS}	Transconductance		12		S	V _{DS} = 20 V, I _D = 20A, T _J = 25 °C	Fig. 5
			11		S	V _{DS} = 20 V, I _D = 20A, T _J = 175 °C	
C _{iss}	Input Capacitance		1100		pF	V _{GS} =0V, V _{DS} =400 V, f=1MHz V _{AC} =25 mV	Fig. 9
C _{oss}	Output Capacitance		56				
C _{rss}	Reverse Transfer Capacitance		15				
E _{ON}	Turn-On Switching Energy		110				
E _{OFF}	Turn-Off Switching Energy		32		µJ	V _{DS} =400V, V _{GS} =-5/18V, I _D = 20A, R _{G(ext)} = 0Ω	
t _{d(on)}	Turn-On Delay Time		15				
t _r	Rise Time		45				
t _{d(off)}	Turn-Off Delay Time		13				
t _f	Fall Time		10		ns	V _{DD} =400V, V _{GS} =-0/20 V I _D = 20A, Timing relative to V _{DS}	
R _{G(int)}	Internal Gate Resistance		6.0				
Q _{gs}	Gate to Source Charge		21		nC	V _{DD} =400V, V _{GS} =-0/20 V I _D = 20A	Fig. 10
Q _{gd}	Gate to Drain Charge		14				
Q _g	Total Gate Charge		75				

Reverse Diode Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V _{SD}	Diode Forward Voltage	3.4		V	V _{GS} = -5V, I _{SD} = 10 A, T _J = 25 °C	Fig. 7
		3.2		V	V _{GS} = -5V, I _{SD} = 10 A, T _J = 175 °C	
I _S	Continuous Diode Forward Current		30	A	T _C = 25 °C	
t _{rr}	Reverse Recovery time	20		ns	V _{GS} = -5V, I _{SD} = 20 A, V _R = 400V, dif/dt=1200A/µs;	
Q _{rr}	Reverse Recovery Charge	65		nC		
I _{rrm}	Peak Reverse Recovery Current	8		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Unit	Test Conditions	Note
R _{θJC}	Thermal Resistance from Junction to Case	0.95	°C/W		Fig. 12
R _{θJA}	Thermal Resistance From Junction to Ambient	35			



Typical Performance


Figure 1. Output Characteristics $T_J = -55^{\circ}\text{C}$

Figure 2. Output Characteristics $T_J = 25^{\circ}\text{C}$




Figure 3. Output Characteristics $T_J = 175^{\circ}\text{C}$




Figure 4. On-Resistance For Various Gate Voltage




Figure 5. Transfer Characteristic for Various Junction Temperatures




Figure 6. Threshold Voltage vs. Temperature




Figure 7. Body Diode Characteristics, $T_J = 25^\circ\text{C}$










Figure 8. Body Diode Characteristics, $T_J = 175^\circ\text{C}$



Package Dimensions: TO-247-3L


符号	机械尺寸/mm		
	最小值	典型值	最大值
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.90	2.00	2.10
b	1.10	1.20	1.35
b1		2.00	
b2		3.00	
c	0.55	0.60	0.75
D	20.80	21.00	21.20
D1		16.55	
D2		1.20	
E	15.60	15.80	16.0
E1		13.30	
E2		5.00	
E3		2.50	
e		5.44	
L	19.42	19.92	20.42
L1		4.13	
P	3.50	3.60	3.70
P1	-	-	7.40
P2		2.50	
Q		5.80	
S	6.05	6.15	6.25
T		10.00	
U		6.20	

