




## WGU4N65SE

### Features:

- Low Intrinsic Capacitances.
- Excellent Switching Characteristics.
- Extended Safe Operating Area.
- Unrivalled Gate Charge : $Q_g = 14\text{nC}$  (Typ.).
- $BVDSS = 650\text{ V}$ ,  $I_D = 4\text{A}$
- $R_{DS(on)} : 2.50\Omega$  (Max) @  $V_G = 10\text{V}$
- 100% Avalanche Tested

TO-251



- 1.Gate (G)
- 2.Drain (D)
- 3.Source (S)

### Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
$V_{DSS}$	Drain-Source Voltage	650	V
$I_D$	Drain Current	4.0	A
		2.7	
$V_{GS(TH)}$	Gate Threshold Voltage	30	V
$E_{AS}$	Single Pulse Avalanche Energy (note1)	120	mJ
$I_{AR}$	Avalanche Current (note2)	4.0	A
$P_D$	Power Dissipation ( $T_j = 25^\circ\text{C}$ )	50	W
$T_j$	Junction Temperature(Max)	150	°C
$T_{stg}$	Storage Temperature	-55~+150	°C
TL	Maximum lead temperature for soldering purpose, 1/8 from case for 5 seconds	300	°C

### Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JC}$	Thermal Resistance,Junction to Case	-	2.4	°C/W
$R_{\theta JA}$	Thermal Resistance,Junction to Ambient		62.5	°C/W

## Electrical Characteristics (Ta=25°C unless otherwise noted)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
Off Characteristics						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	I <sub>D</sub> =250 μA , V <sub>GS</sub> =0	650	-	-	V
△BV <sub>DSS</sub> /△T <sub>J</sub>	Breakdown Voltage Temperature Coefficient	I <sub>D</sub> =250 μA , Reference to 25°C	-	0.67	-	V/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =650V, V <sub>GS</sub> =0V	-	-	10	μA
		V <sub>DS</sub> =520V, T <sub>J</sub> =125°C			100	
I <sub>GSSF</sub>	Gate-body leakage Current, Forward	V <sub>GS</sub> =+30V, V <sub>DS</sub> =0V	-	-	100	nA
I <sub>GSSR</sub>	Gate-body leakage Current, Reverse	V <sub>GS</sub> =-30V, V <sub>DS</sub> =0V	-	-	-100	
On Characteristics						
V <sub>GS(TH)</sub>	Date Threshold Voltage	I <sub>D</sub> =250μA, V <sub>DS</sub> =V <sub>GS</sub>	2	-	4	V
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance	I <sub>D</sub> =2.0A, V <sub>GS</sub> =10V	-		2.5	Ω
Dynamic Characteristics						
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =25V , V <sub>GS</sub> =0 , f=1.0MHz	-	560	-	pF
C <sub>oss</sub>	Output Capacitance		-	48	-	
C <sub>rss</sub>	Reverse Transfer Capacitance		-	5.4	-	
Switching Characteristics						
T <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =325V , I <sub>D</sub> =4A R <sub>G</sub> =25Ω (Note 3,4)	-	25		nS
T <sub>r</sub>	Turn-On Rise Time		-	45		
T <sub>d(off)</sub>	Turn-Off Delay Time		-	25		
T <sub>f</sub>	Turn-Off Rise Time		-	35		
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =520V, V <sub>GS</sub> =10V , I <sub>D</sub> =4A (Note3,4)	-	14.3		nC
Q <sub>gs</sub>	Gate-Source Charge		-	2.8	-	
Q <sub>gd</sub>	Gate-Drain Charge		-	4.5	-	
Drain-Source Diode Characteristics and Maximum Ratings						
I <sub>s</sub>	Max. Diode Forward Current	-		--	4	A
I <sub>SM</sub>	Max. Pulsed Forward Current	-		--	16	
V <sub>SD</sub>	Diode Forward Voltage	I <sub>D</sub> =4A	-	-	1.4	V
T <sub>rr</sub>	Reverse Recovery Time	I <sub>s</sub> =4A, V <sub>GS</sub> =0V dI/dt=100A/μs (Note3)	-	393	-	nS
Q <sub>rr</sub>	Reverse Recovery Charge		-	1.5	-	μC







Notes : 1, L=0.5mH, IAS= 4A, VDD=50V, RG=25Ω , Starting TJ =25°C

2, Repetitive Rating : Pulse width limited by maximum junction temperature






3, Pulse Test : Pulse Width ≤ 300μs, Duty Cycle ≤ 2%

4, Essentially Independent of Operating Temperature



## Typical Characteristics




## Typical Characteristics (Continued)




## Gate Charge Test Circuit &amp; Waveform




## Switching Test Circuit




## Switching Waveforms





## Gate Charge Test Circuit



## Gate Charge Waveform




## Peak Diode Recovery dv/dt Test Circuit &amp; Waveform



## Package Dimension

T0-251

Unit:mm



Symbol	Dimensions In Millimeters		Symbol	Dimensions In Millimeters	
	Min	Max		Min	Max
A	6.45	6.75	a	0.70	0.90
A1	5.20	5.40	b	9.00	9.40
B	5.95	6.25	c	0.45	0.55
B1	0.95	1.25	c1	0.45	0.55
C	2.20	2.40	e1	2.24	2.34
C1	0.95	1.15	e	4.43	4.73