



Product: [2118A](#)

Fieldbus, 1 Pr #18 Str TC, XLPO Ins, OS, TPE Jkt, 600V TC

[Request Sample](#)

Product Description

Fieldbus, 1 Pair 18AWG (7x26) Tinned Copper, XLPO Insulation, Overall Beldfoil® Shield, Orange TPE Outer Jacket, 600V TC

Technical Specifications

Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	18	7x26	TC - Tinned Copper

Insulation

Material	Color Code
XLPE - Cross-Linked Polyethylene (Thermoset)	Blue, Orange and Numbered

Inner Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
	Tinned Copper (TC)	

Outer Shield

Material
Bi-Laminate (Alum+Poly)

Outer Jacket

Material	Nom. Diameter	Ripcord
TPE - Thermoplastic Elastomer	0.319 in	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Capacitance Unbalance	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
5.86 Ohm/1000ft (19.2 Ohm/km)	1.2 pF/ft (3.9 pF/m)	22 pF/ft	100 Ohm	64%	8.7 Amps per Conductor

High Frequency (Nominal/Typical)

Nom. Insertion Loss (Attenuation)
0.08 dB/100ft

High Frequency

Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.091 dB/100ft	100 Ohm

Voltage

UL Voltage Rating

600 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Wet/Dry	-25°C Cold Impact -40°C to +90°C -55°C Cold Bend

Max. Pull Tension:	57 lbs (26 kg)
Bulk Cable Weight:	51 lbs/1000ft (76 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1581 Vertical Tray, 1202, IEC 60332-3-24
NEC / UL Compliance:	Article 336, TC-ER
AWM Compliance:	AWM I A/B II A/B, C22.2 #230 Type TC; C22.2#239 Type CIC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.505 Revision Date: 05-03-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
2118A 0061000	Blue, Light	Reel	1,000 ft	612825129479
2118A 0065000	Blue, Light	Reel	5,000 ft	612825129486
2118A 0035000	Orange	Reel	5,000 ft	612825129462

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.