
DATE	REV	ECN	APP'D. BY
09/08/21	A0	11830	ADB
09/16/21	A1	11846	ADB
09/23/21	A2	11849	ADB
12/13/22	А3	12082	GWL



VIEW Z-Z SCALE 1:1 PER EIA/TIA 568B В

NOTES:

1. M12 CONNECTOR COMPONENTS:

HOUSING: THERMOPLASTIC UL94 V-0

SCALE 1:1

PER EIA/TIA 568B

CONTACTS: COPPER ALLOY

SHELL: COPPER ALLOYS AND ZINC ALLOY

SEALING: NBR

CONTACT PLATING: UNDERPLATE: 50u"~70u" NICKEL CONTACT AREA: 10u" GOLD

CABLE CONSTRUCTION:

CONDUCTOR: 26 AWG 7/34 STRANDED TINNED COPPER

INSULATION: HIGH DENSITY POLYETHYLENE

CABLE: (4) TWISTED PAIRS TWISTED TOGETHER AND WRAPPED WITH A FOAM POLYPROPYLENE TAPE TO FORM CABLE CORE

SHIELD: 38 AWG TINNED COPPER BRAID OVER CABLE CORE. A SECOND

SHIELD OF ALUMINIZED POLYESTER FOIL OVER BRAID

JACKET: ZHFR POLYURETHANE, TEAL, .261 DIAMETER. NOMINAL PULL FORCE OF COIL**: F(LBS)=(1.35 * X)-1.00 X=(EXPANDED LENGTH) / (CONTRACTED LENGTH)

2. ELECTRICAL TESTING:


100% TRANSMISSION TESTED FOR CAT 5E CHANNEL PERFORMANCE, WIRE MAP, CONTINUITY, SHORTS, DWV AT 500 VDC

3. PACKAGING:


ONE CABLE PER BAG

P/N STRUCTURE:

BM-CBMMxxxFA



PIN ASSIGNMENT



568B STANDARD WIRING MAP

PIN NUMBER / WIRE COLOR CROSS REFERENCE				
IEC 61076-2-109	TIA/EIA 568B	WIRE COLOR		
1	1	WHITE-ORANGE		
2	2	ORANGE		
3	3	WHITE-GREEN		
4	6	GREEN		
5	7	WHITE-BROWN		
6	8	BROWN		
7	5	WHITE-BLUE		
8 4		BLUE		

THIRD ANGLE PROJECTION

Z <---



11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512

http://www.stewartconnector.com

PART NUMBER COIL LENGTH MAX EXT LENGTH ≈ COIL O.D. BM-CBMM001F5 1 FT [.3M] 6 FT [1.8M] 1.25 IN [31.75mm] 18 FT [5.5M] BM-CBMM003F5 3 FT [.9M] 1.25 IN [31.75mm] BM-CBMM005F5 5 FT [1.5M] 30 FT [9.1M] 1.25 IN [31.75mm]]

42 FT [12.8M]

1.25 IN [31.75mm]

7 FT [2.1M]

PART NUMBERS REFERENCE TABLE

RoHS

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS: INCHES [METRIC] UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.008 [0.20] ANGLES ARE ± 1° SHEET NO. 1 OF 1

DO NOT SCALE DRAWING

MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR, ONE OR MORE U.S. PATENTS

02-19-21 GWL APPD BY: ADB 09-08-21 CT999249

USE FOR APPROXIMATION ONLY. VALIDATION BASED ON 1 FT LONG COIL BODY 1.25 O.D

AutoCAD

M12 X-CODE MALE TO M12 X-CODE MALE COIL CORD

BM-CBMM007F5