

## ATGBICS XDACBL3M Intel Compatible Direct Attach Copper Twinax Cable 10G SFP+ Cu (3m, Passive)

**Brand :** ATGBICS

**Product code:** XDACBL3M-C

**Product name :** XDACBL3M Intel Compatible Direct Attach Copper Twinax Cable 10G SFP+ Cu (3m, Passive)

XDACBL3M Intel Compatible Direct Attach Copper Twinax Cable 10G SFP+ Cu (3m, Passive)

ATGBICS XDACBL3M Intel Compatible Direct Attach Copper Twinax Cable 10G SFP+ Cu (3m, Passive):

ATGBICS XDACBL3M compatible 10GBase-CU SFP+ to SFP+ direct attach cable operates over passive copper with a cable length of 3m. It is suitable for short reach connection between two SFP+ ports in 10G interconnecting networking applications. Our product meets the specification of Intel XDACBL3M and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols including; 1x InfiniBand QDR, DDR, SDR, 10G Gigabit Ethernet, Fibre Channel, MSA SPF+ SFF-8431, SFF-8432, and SFF-8472 compliant.

ATGBICS XDACBL3M Intel Compatible Direct Attach Copper Twinax Cable 10G SFP+ Cu (3m, Passive). Cable length: 3 m, Connector 1: SFP+, Connector 2: SFP+, Data transfer rate: 10000 Mbit/s



### Features

Product colour *	Black
Cable length *	3 m
Connector 1 *	SFP+
Connector 2 *	SFP+
Connector 1 gender *	Male
Connector 2 gender *	Male
Jacket material	Polyvinyl chloride (PVC)
Conductor material	Copper
Ethernet interface type	10 Gigabit Ethernet
Networking standards	IEEE 802.3ae
AWG wire size	30
Data transfer rate	10000 Mbit/s
Plug and Play	✓
Certification	CE, FCC, RoHS

### Features

Country of origin	United Kingdom
-------------------	----------------

### Operational conditions

Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-40 - 80 °C
Operating relative humidity (H-H)	10 - 90%
Storage relative humidity (H-H)	10 - 85%

### Packaging data

Quantity per pack	1 pc(s)
-------------------	---------

### Technical details

Sustainability compliance	✓
Sustainability certificates	RoHS
Doesn't contain	Lead



5056468721754

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date