



Product: [FSSL036NG](#)

Outdoor Loose Tube OS2 36 Fibers

Product Description

FX Outdoor Loose Tube OS2 36 Fibers OSP Sub-Units(12F) Gel Black

Technical Specifications

Product Overview

|                        |                                          |
|------------------------|------------------------------------------|
| Suitable Applications: | Campus Area Network, Long Haul, Backbone |
|------------------------|------------------------------------------|

Fiber Specifications

|                      |            |
|----------------------|------------|
| Fiber Type:          | OS2        |
| Fiber Core Diameter: | 8.2/125 µm |
| Fiber Diameter:      | 250 µm     |
| Fiber Count:         | 36         |
| Fiber Color Coding:  | TIA-598-D  |

Cable Construction

|                            |                    |
|----------------------------|--------------------|
| Number of Active Subunits: | 3                  |
| Number of Fillers:         | 3                  |
| Fibers Per Subunit:        | 12                 |
| Subunit Waterblocking:     | Gel Filled         |
| Subunit Diameter:          | 0.098 in (2.5 mm)  |
| Central Strength Member:   | GRP                |
| Core Wrap:                 | Waterblocking Tape |
| Cable Core Waterblocking:  | Waterblock Tape    |

Inner Jacket Specifications

|           |                   |
|-----------|-------------------|
| Material: | PE - Polyethylene |
|-----------|-------------------|

Outer Jacket Specifications

|                     |                            |
|---------------------|----------------------------|
| Strength Member:    | Waterblocking Aramid Yarns |
| Jacket Material:    | PE - Polyethylene          |
| Nom. Diameter:      | 0.410 in (10.4 mm)         |
| Color:              | Black                      |
| Number of Ripcords: | 1                          |

Optical Characteristics

| Wavelength                      | 1310 nm    | 1550 nm    |
|---------------------------------|------------|------------|
| Max. Attenuation                | 0.40 dB/km | 0.30 dB/km |
| Mode Field Diameter             | 9.2 µm     | 10.4 µm    |
| 1 Gigabit Ethernet Performance  | 5,000 m    | --         |
| 10 Gigabit Ethernet Performance | 10,000 m   | 40,000 m   |

Mechanical Characteristics

|                                       |              |
|---------------------------------------|--------------|
| Min. Bend Radius During Installation: | 15x Cable OD |
|---------------------------------------|--------------|

|                                            |                       |
|--------------------------------------------|-----------------------|
| Min. Bend Radius During Operation:         | 10x Cable OD          |
| Max. Tensile Strength During Installation: | 2670 N (600 lbf)      |
| Max. Tensile Strength During Operation:    | 800 N (180 lbf)       |
| Crush Resistance:                          | 220 N/cm              |
| Bulk Cable Weight:                         | 47 lbs/kft (70 kg/km) |

Temperature Range

|                                 |              |
|---------------------------------|--------------|
| Installation Temperature Range: | -30C to +70C |
| Operating Temperature Range:    | -40C to +70C |
| Storage Temperature Range:      | -40C to +75C |

Standards and Compliance

|                            |                                                                              |
|----------------------------|------------------------------------------------------------------------------|
| Environmental Suitability: | Outdoor, Burial                                                              |
| Sustainability:            | CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available |
| ICEA Compliance:           | S-87-640                                                                     |
| TIA/EIA Compliance:        | ANSI/ICEA S-87-640                                                           |

History

|                      |                                                 |
|----------------------|-------------------------------------------------|
| Update and Revision: | Revision Number: 0.81 Revision Date: 11-09-2022 |
|----------------------|-------------------------------------------------|

Part Numbers

Variants

| Item #    | Color | Putup Type | UPC          |
|-----------|-------|------------|--------------|
| FSSL036NG | Black | Reel       | 612825372592 |

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.