


400G Multimode 50/125 OM4 Fiber Optic Cable
(Duplex SN-PC M/M), LSZH, Magenta, 3 m (9.8 ft.)

MODEL NUMBER: N823S-03M-MG



400 GbE Ethernet cable supports high bandwidths necessary for next-gen cloud services, hyperscale data centers and telecom carriers.

Features

400 GbE Cable Supports High Bandwidths for High-Density Data Networking

The N823S-03M-MG is a premium multimode fiber optic cable that supports 400 Gb Ethernet speeds for transmitting data and voice signals over short distances. As the amount of traffic in data networks grows, so does the need for next-generation devices and fiber cables to support much higher bandwidths in hyperscale, edge, enterprise and colocation data center interconnect (DCI) applications where density and speed are both very important.

Compact SN Connectors Designed for the Latest OSFP/QSFP-DD Transceivers

This 400 Gb cable features duplex SN connectors on both ends. SN connectors are four times smaller than standard LC connectors and provide individual and independent duplex fiber support for OSFP/QSFP-DD transceivers. Push/pull boots encourage dense vertical stacking within a crowded patch panel or switch and make the cable easy to install or remove with just one hand. The switchable SN/PC ends let you make quick polarity changes in the field without tools or the need to re-terminate the connectors.

Magenta-Colored Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OM4-rated cable has a magenta jacket to identify it as multimode in a crowded patch panel or switch and prevent it from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas.

Highlights

- Duplex SN connectors optimized for the latest 400 Gb OSFP/QSFP-DD transceivers
- Space-saving SN plugs are 4x smaller than standard LC for easier cable management
- Switchable connectors allow polarity conversion without tools or re-termination
- Compact push/pull boots allow easy installation/removal with just one hand
- Magenta LSZH jacket allows fast identification in a crowded switch or patch panel

Package Includes

N823S-03M-MG 400G Multimode 50/125 OM4 Fiber Cable, Magenta, 3 m (9.8 ft.)

Specifications

OVERVIEW	
UPC Code	037332274564
Technology	Multimode
Optical Mode	OM4

Mode Type	Multimode
PHYSICAL	
Cable Jacket Color	Magenta
Connector Color	Aqua; White
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Cable Outer Diameter (OD)	1.60 mm
Clad Diameter (microns)	125.0
Core Diameter (microns)	50.0
Primary Coating Diameter (microns)	245.0
Number of Fibers	2
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (in.)	118.1
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Fiber Cable Length	3M (9.8 ft)
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 85% RH, Non-Condensing
COMMUNICATIONS	
Network Compatibility	400 Gbps
Wavelength	1300nm; 850nm
Attenuation @ 850NM	3.5dB
Attenuation @ 1300NM	1.5dB
Insertion Loss	< 0.20 dB
CONNECTIONS	
Side A - Connector 1	SN DUPLEX (MALE)
Side B - Connector 1	SN DUPLEX (MALE)
Endface Polish	PC
Switchable Polarity	Yes

FEATURES & SPECIFICATIONS	
Push/Pull Tabs	No
Breakout	No
Trunk	No
Optical Port	SN
STANDARDS & COMPLIANCE	
Product Certifications	UL 1651
Product Compliance	RoHS; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty