

RT-770-1/2-0-SP

✓ ACTIVE

RAYCHEM


TE Internal #: D56022-000

Black, 2:1, Single Wall Tubing, Shrinks To .25 in [6.4 mm],
Crosslinked Fluoroelastomer, .5 in [12.7 mm] Inner Diameter, Highly
Flame-Retardant, Piece

[View on TE.com >](#)



Heat Shrink Tubing > Single Wall RT 770: Heat Shrink Tubing, 2:1 Shrink Ratio



Primary Product Color: **Black**
Wall Type: **Single Wall**
Expanded Inside Diameter (Min): **12.7 mm [.5 in]**
Recovered Inside Diameter (Max): **6.4 mm [.25 in]**
Shrink Ratio: **2:1**

[All Single Wall RT 770: Heat Shrink Tubing, 2:1 Shrink Ratio \(10\)](#)

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Body Features

Fluid Type	Aviation Fuel, Brake Fluid, Chemicals /Solvents, De-Icing Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Military Decontaminating Agents, Water
Material Systems Code	770
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Crosslinked Fluoroelastomer
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.08 mm[.003 in]
Expanded Inside Diameter (Min)	12.7 mm[.5 in]
Recovered Inside Diameter (Max)	6.4 mm[.25 in]
Tubing Size Range	6.4 – 12.7 mm[.25 – .5 in]

Usage Conditions

Shrink Temperature (Min)	150 °C
--------------------------	--------



Resistance Properties	Moisture
Tubing Flammability Type	Highly Flame-Retardant
Operating Temperature Range	-55 – 125 °C
Recovery Temperature	150 °C

Operation/Application

Mechanical Resistance	Fluids
-----------------------	--------

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Packaging Features

Packaging Method	Piece
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #878514-000
222K152-25-0



TE Part #2041441-2
DP 20P V/T DIP 15u" Au, 2.5 tails



TE Part #1-2176324-9
SMV 3W 3M3 5%



TE Part #1393304-9
V23134J1052D642-EV-CBOX



TE Part #EM4253-000
242W042-3-G01-0




TE Part #456425-000
222K121-3-CS-1821-0



TE Part #610580-ZZ
PIN CONTACT ASSEMBLY



TE Part #CV1694-000
TXR54AG00-1005AI-CS-2112



TE Part #CH4241-000
TXS127AB00-1206BI-CS-2112

Documents

Product Drawings

RT-770-1/2-0-SP

English

Datasheets & Catalog Pages

raychem-tubing-product-selection-guide

English

1654025_Sec3_RT-770

English

Product Specifications

Product Specification

English



Product Environmental Compliance

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet