


4

3

2

1



NOTES:

1. "□" DENOTES CRITICAL DIMENSIONS
2. Part name: Inlet
3. Power Rating: 15A 120VAC/250VAC
4. Terminal must comply with UL 310 standard
5. Life test: No Load condition: 5,000 cycles
6. Insertion Force: 9±4kg
7. Withdrawal Force: 6±3kg

3	BODY	PBT 4130(a) 94-V0 Black	1
2	PIN 2#	C2680 Tin-plating 3~5μm	1
1	PIN 1#	C2680 Tin-plating 3~5μm	3
NO. PART NAME MATERIAL			Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.4					MAT'L	***		
2	修改进胶口	7	→	X.X	±0.3					MATERIAL NO.		DRAWING NO.	REV.
1	增加限位筋条	6	→	X.XX	±0.2								
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD				RT-C05A-A		WIF111001	A2

4

3

2

1