



Connectors > Connector Accessories > Connector Backshells > Backshells, DEUTSCH DTM



Connector Backshell Product Type: **Backshell**

Primary Product Material: **PA GF**

Number of Positions: **4**

Sealable: **No**

Operating Temperature Range: **-55 – 125 °C [-67 – 257 °F]**

[All Backshells, DEUTSCH DTM \(12\)](#)

Features

Product Type Features

Connector Backshell Product Type	Backshell
Sealable	No

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Primary Product Material	PA GF

Dimensions

Compatible Cable Diameter Range	0 – 8.5 mm[0 – .225 in]
---------------------------------	-------------------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]



Industry Standards

IP Rating	IP6K9K
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D485-CH8172
DEUTSCH DTM Housings



TE Part # DTMH06-4SA
PLG, 4P, BLK, N, HI TEMP, A



TE Part # DTMH04-4PD
REC, 4P, BLK, N, HI TEMP, D



TE Part # DTMH04-4PB
REC, 4P, BLK, N, HI TEMP, B



TE Part # DTMH04-4PC
REC, 4P, BLK, N, HI TEMP, C



TE Part # DTMH06-4SB
PLG, 4P, BLK, N, HI TEMP, B



TE Part # DTMH06-4SC
PLG, 4P, BLK, N, HI TEMP, C




TE Part # DTMH06-4SD
PLG, 4P, BLK, N, HI TEMP, D

Also in the Series | **DEUTSCH DT**



Automotive Connector Caps & Covers
(19)



Automotive Connector Locks &
Position Assurance(74)




Automotive Housings(620)




Connector Backshells(58)



Connector Seals & Cavity Plugs(6)




Connector Strain Relief(28)



Insertion & Extraction Tools(3)



Other Automotive Connector
Accessories(27)




PCB Headers & Receptacles(103)

Also in the Series | **DEUTSCH DTM**



Automotive Connector Caps & Covers (7)



Automotive Connector Locks & Position Assurance(17)



Automotive Housings(100)



Connector Backshells(6)



Connector Strain Relief(28)



Insertion & Extraction Tools(2)



PCB Headers & Receptacles(36)

Customers Also Bought



TE Part #2035366-7
Backshell,AS16,4P,90Deg,NC08,LP, Plug



TE Part #DTMH06-2SA
PLG, 2P, BLK, N, HI TEMP, A



TE Part #1028-041-0205
Backshells, DEUTSCH DTM




TE Part #HD10-9-96PE-B025
RECP ASM




TE Part #0528-004-3805
BKSHL, 38P, BLK, PLG, RA



TE Part #2-1703773-1
6POS,TAB 1.6X0.6,PIN HSG,ASSY



TE Part #2293821-1
HDP24-18-8PE-L024, REC, 8P, E, THD, 12,P



TE Part #DTP2P-BT-BK
BOOT, 2P, REC, ST, BLK

Documents

Product Drawings

BKSHL, 4P, BLK, REC, ST, NW 8.5

English

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_1028-027-0405_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1028-027-0405_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1028-027-0405_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Engineering Report](#)

English