

2323857-1  ACTIVE


TE Internal #: 2323857-1

Busbar to R-terminal Cable Assembly, .24 m, 8 mm² / 18 mm²,
White / Black / Green Cable, Double Ended, Busbar Plug, R-
terminal, Thermoplastic

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Power Cable Assemblies



Cable Assembly Configuration: **Double Ended**

Wire Size: **8 mm², 18 mm²**

Outside Cable Diameter: **[.08 in, .24 in]**

Cable Assembly Length: **.24 m**

Cable Color: **Black, Green, Red, White**

Features

Product Type Features

Cable Assembly Type	Busbar to R-terminal
Connector Type (End A)	Busbar Plug
Connector Type (End B)	R-terminal

Body Features

Cable Color	Black, Green, Red, White
Connector Color (End A)	Black

Housing Features

Housing Material	Thermoplastic
------------------	---------------

Dimensions

Wire Size	8 mm ² , 18 mm ²
	.08 in [.24 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C
-----------------------------	--------------

Other

Cable Assembly Configuration

Double Ended

Cable Assembly Length

.24 m

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.

Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1490534-1
HYP10 PLASTI-GRIP 8AWG DIE SET



TE Part # 69959
HHHT AMPLI-BOND PG 8 ASSY



TE Part # 601129-2
HAND TOOL (A.S.I.)

Customers Also Bought



Documents

Product Drawings

CA, 50A TRIBUTARY

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2323857-1_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2323857-1_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2323857-1_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.