



- Socket : RT-C14-F0B-AA
- Rating : 10A 250VAC VDE CCC
15A 250VAC UL CUL
 - Insulation resistance : >100MΩ Min 500VDC
 - Dielectric strength : >2000VAC 1 minute
- Switch : SS11-BBIWG-R20-R
- Rating : 16A 125/250VAC (UL;C-UL);
12A 125/250VAC (UL;C-UL);
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)
 - Contact resistance : <50mΩ
 - Insulation resistance : >100MΩ (500VDC between open contacts)
 - Dielectric strength : >1500VAC 0.5mA 1 minute

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE					SCALE	FIT		
3	→	8	→	X	±0.3				LMC 2018.07.07	MAT'L	***	DRAWING NO. REV.	
2	→	7	→	X.X	±0.2					MATERIAL NO.			
1	→	6	→	X.XX	±0.1					RT-C14-F1+SS11-1 BB	*****	A	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD							

4

3

2

1