



Product: [5542FE](#)

Security & Sound, #22-3pr, BC, Shielded, CMR

Product Description

Security & Sound Cable, Riser-CMR, 3-22 AWG stranded bare copper pairs with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	3	22	7x30	BC - Bare Copper

Insulation			
Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PO - Polyolefin	0.008 in (0.20 mm)	0.045 in (1.1 mm)	Black & Red, Black & White, Black & Green

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket			
Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.189 in (4.80 mm)	Yes

Electrical Characteristics

Electricals			
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
17.6 Ohm/1000ft	24 pF/ft (79 pF/m)	43.25 pF/ft (141.9 pF/m)	2 Amps per Conductor at 25°C

Voltage	
UL Voltage Rating	
300 V	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius	
Stationary Min.	Installation Min.
1.89 in (48.0 mm)	1.89 in (48.0 mm)

Max. Pull Tension:	60 lbs (27 kg)
--------------------	----------------

Bulk Cable Weight:	23 lbs/1000ft
--------------------	---------------

Standards and Compliance

Flammability / Reaction to Fire:	UL 1666 riser, FT4
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6542FE

History

Update and Revision:	Revision Number: 0.413 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
5542FE 0081000	Gray	612825164333
5542FE 008U1000	Gray	612825164326

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.