

P1CA-SAMSAM-141CC-6

SMA Male to SMA Male cable assembly using 141CC Conformable Coax, 6 inch, frequency to 26.5 GHz.

Product Features

P1CA-SAMSAM-141CC-6 is an RF Cable that is part of P1dB's YouForm™ conformable cable assembly series. It is a 6 inch SMA Male to SMA Male Conformable cable assembly that utilizes 141CC conformable coax with a diameter of 0.141 inches. Frequency is DC to 26.5 GHz with a max VSWR of 1.35:1.



Electrical Specification: T_{Ambient} = 25° C

Parameter	Frequency Range	Units	Min	Typical	Max	Notes
Frequency Range		GHz	DC		26.5	
VSWR	DC to 1.0	1:			1.1	
	1.0 to 5.0				1.1	
	5.0 to 10.0				1.15	
	10.0 to 26.5				1.35	
Insertion Loss	DC to 1.0	dB/ft.			0.12	
	1.0 to 5.0				0.31	
	5.0 to 10.0				0.45	
	10.0 to 26.5				0.65	
Velocity Of Propagation		%		70.0		

Mechanical And Environmental Specifications:

Parameter	Description	Notes
Connector 1	SMA Male	
Connector 1 Coupling Nut	Passivated Stainless Steel	
Connector 1 Body	Gold Plated Brass	
Connector 1 Contact	Gold Plated Brass	
Connector 2	SMA Male	


P1CA-SAMSAM-141CC-6

SMA Male to SMA Male cable assembly using 141CC Conformable Coax, 6 inch, frequency to 26.5 GHz.



Parameter	Description	Notes
Connector 2 Coupling Nut	Passivated Stainless Steel	
Connector 2 Body	Gold Plated Brass	
Connector 2 Contact	Gold Plated Brass	
Coax Cable	Conformable	
Cable Type	141CC	
Cable Inner Conductor	SPCW	
Dielectric	PTFE	
Shield	1. Tinned Cu/Sn Braid	
Jacket	FEP	
Coax Diameter	0.141	
Minimum Bend Radius	0.38	
Length	6.0	
RoHS Compliance	Yes	

Drawing



Product Notes

Part marking:

Parts may be labeled either P1CA-SAMSAM-141CC-6 or P1CA-SAMSAM-141CC-06.