



**Product:** [5508UE](#)

Security & Sound, #22-10c, BC, CMR

**Product Description**  
Security & Sound Cable, Riser-CMR, 10-22 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

**Technical Specifications**

**Product Overview**

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	10	22	7x30	BC - Bare Copper

**Insulation**

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PP - Polypropylene	0.008 in (0.20 mm)	0.062 in (1.6 mm)	Black, Red, White, Green, Brown, Blue, Orange, Yellow, Purple, Gray

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.214 in	Yes

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
17.41 Ohm/1000ft	22.7 pF/ft (74.5 pF/m)	2 Amps per Conductor at 25°C

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
75°C	-20°C To +75°C

**Bend Radius**

Stationary Min.	Installation Min.
2.14 in (54.4 mm)	2.14 in

Max. Pull Tension:	91 lbs (41 kg)
Bulk Cable Weight:	32 lbs/1000ft

**Standards and Compliance**

Environmental Suitability:	Outdoor
----------------------------	---------

Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6508UE

History

Update and Revision:	Revision Number: 0.303 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5508UE.00305	Chrome	Reel	305 m	8719605008800	
5508UE 0081000	Gray			612825163961	C
5508UE 008U1000	Gray			612825163954	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.