

EG41086001

✓ ACTIVE

RAYCHEM | RAYCHEM ES-CAP

TE Internal #: EG41086001

Heat Shrink Caps, Dual Wall Wall, Adhesive Precoat, -40 – 105 °C

[-40 – 221 °F], RAYCHEM ES-CAP

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Caps

Wall Type: **Dual Wall**Adhesive Requirement: **Adhesive Precoat**Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Wall Type	Dual Wall
-----------	-----------

Configuration Features

Modification	B8
Adhesive Requirement	Adhesive Precoat

Body Features

Sealant Type	Anti-Flux
Lining Type	Adhesive
Shrink Ratio	4:1
Primary Product Material	Crosslinked Polyolefin
Flexibility	Semi-Rigid
Primary Product Color	Black

Dimensions

Recovered Wall Thickness (Nominal)	1.91 mm[.075 in]
Recovered Inside Diameter (Max)	2.41 mm[.095 in]
Expanded Inside Diameter (Min)	10.8 mm[.425 in]
Compatible Cable Diameter Range	10.9 mm[.43 in]
Wall Thickness	Thin
Product Length	40 mm[1.575 in]

Usage Conditions

Flammability Requirement	Flame-Retardant
Fluid Resistance Type	Automatic Transmission Fluid, Brake Fluid, Diesel Fuel, Engine Cleaner, Engine Coolant, Lubricating Oil, Power Steering Fluid, Water
Resistance Properties	Limited Immersion Protection, Moisture & Spray Protection, Splash Protection
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Identification Marking

Marked	No.3
--------	------

Industry Standards

UL Rating	Recognized
-----------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides


on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM ES-CAP



Heat Shrink Caps(40)

Customers Also Bought




TE Part #1-1718346-3
MQS, CONNECTOR HOUSING



TE Part #62336-1
110 FASTON FLAG REC 22-18 AWG
TPBR




TE Part #1-963736-2
TAB 5.8x0.8 CONTACT CS SRC Ag



TE Part #1718188-1
HIGH PRESSURE SOCKET 4MM




TE Part #0989076009
RBK-ILS-125-NR2-0-40MM




TE Part #5129894001
CGPT-9/3-0-SP



TE Part #1803126-1
CRIMPER, WIRE F NON-TYPICAL RK
VALUES



TE Part #238011-4
SPACER, BLOCK CRIMPER (.104)



TE Part #9-539939-3
TRANSPORTFINGER

Documents

Product Drawings

[ES-CAP-NO.3-B8-0-40MM](#)

English

Datasheets & Catalog Pages

[Measuring_Single_Wall_Tubing](#)

English

[ES Caps Pages from 9-1773447-9](#)

English

[Selecting_Correct_Tubing_1216](#)

English

[ES CAP Data Sheet](#)

English

Product Specifications

[Application Specification](#)

English