

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB socket strip (1x 37-position); cable length: 3 m



Commercial data

Item number	2908518
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK2136
Catalog page	Page 573 (C-5-2019)
GTIN	4055626305974
Weight per piece (including packing)	670.1 g
Weight per piece (excluding packing)	670.1 g
Customs tariff number	85444290
Country of origin	DE

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 2 A (Uncoiled, see derating)

Cable/line

Cable length	3 m
Number of positions	37
Shielded	yes
Conductor type	Assembled, shielded, halogen-free round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	37x 0.25 mm ²
Wire diameter incl. insulation	1.2 mm ±0.05 mm
External cable diameter	10.8 mm ±0.5 mm
Outer sheath, material	Halogen-free sheath
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 80 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (at 20 °C)
Smallest bending radius, fixed installation	90 mm
Smallest bending radius, movable installation	170 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	yes
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable)
Resistance to oil	can withstand occasional splashes (raw cable)

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

color code

D-SUB37 (1)	D-SUB37 (1) = white
D-SUB37 (2)	D-SUB37 (2) = brown
D-SUB37 (3)	D-SUB37 (3) = green
D-SUB37 (4)	D-SUB37 (4) = yellow
D-SUB37 (5)	D-SUB37 (5) = gray
D-SUB37 (6)	D-SUB37 (6) = pink
D-SUB37 (7)	D-SUB37 (7) = blue
D-SUB37 (8)	D-SUB37 (8) = red
D-SUB37 (9)	D-SUB37 (9) = black
D-SUB37 (10)	D-SUB37 (10) = violet
D-SUB37 (11)	D-SUB37 (11) = gray-pink
D-SUB37 (12)	D-SUB37 (12) = red-blue
D-SUB37 (13)	D-SUB37 (13) = white-green
D-SUB37 (14)	D-SUB37 (14) = brown-green
D-SUB37 (15)	D-SUB37 (15) = white-yellow
D-SUB37 (16)	D-SUB37 (16) = yellow-brown
D-SUB37 (17)	D-SUB37 (17) = white-gray
D-SUB37 (18)	D-SUB37 (18) = gray-brown
D-SUB37 (19)	D-SUB37 (19) = white-pink
D-SUB37 (20)	D-SUB37 (20) = pink-brown
D-SUB37 (21)	D-SUB37 (21) = white-blue
D-SUB37 (22)	D-SUB37 (22) = brown-blue
D-SUB37 (23)	D-SUB37 (23) = white-red
D-SUB37 (24)	D-SUB37 (24) = brown-red
D-SUB37 (25)	D-SUB37 (25) = white-black
D-SUB37 (26)	D-SUB37 (26) = brown-black
D-SUB37 (27)	D-SUB37 (27) = gray-green
D-SUB37 (28)	D-SUB37 (28) = yellow-gray
D-SUB37 (29)	D-SUB37 (29) = pink-green
D-SUB37 (30)	D-SUB37 (30) = yellow-pink
D-SUB37 (31)	D-SUB37 (31) = green-blue
D-SUB37 (32)	D-SUB37 (32) = yellow-blue
D-SUB37 (33)	D-SUB37 (33) = green-red
D-SUB37 (34)	D-SUB37 (34) = yellow-red
D-SUB37 (35)	D-SUB37 (35) = green-black
D-SUB37 (36)	D-SUB37 (36) = yellow-black
D-SUB37 (37)	D-SUB37 (37) = gray-blue

Connection data

Connection 1

Connection in acc. with standard	IEC 60807-2
	DIN 41652

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable

2908518

<https://www.phoenixcontact.com/us/products/2908518>



Connection method	D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Tightening torque	0.2 Nm
Insertion/withdrawal cycles	> 200
Pitch	2.77 mm

Connection 2

Connection in acc. with standard	IEC 60807-2
	DIN 41652
Connection method	D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Tightening torque	0.2 Nm
Insertion/withdrawal cycles	> 200
Pitch	2.77 mm

Notes

General	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
---------	--


CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

Drawings



Maximum permissible current per path in uncoiled state

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908518>

CSA Approval ID: 70002966	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

cUL Recognized Approval ID: FILE E 238705	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

UL Recognized Approval ID: FILE E 238705	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

EAC Approval ID: RU*-DE.HB*35.B00385
--

cULus Recognized

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable

2908518

<https://www.phoenixcontact.com/us/products/2908518>



Classifications

ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

ETIM

ETIM 8.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable

2908518

<https://www.phoenixcontact.com/us/products/2908518>



Environmental product compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

CABLE-D37SUB/B/B/HF/S/ 3,0M - Cable



2908518

<https://www.phoenixcontact.com/us/products/2908518>

Accessories

KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties,
cable diameter: > 5 mm, lettering field size: 20 x 8 mm

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com