

**EL8197-000**

✓ ACTIVE

**HX-CT**

TE Internal #: EL8197-000

Printable Tubing, Continuous, Low Fire Hazard, 2:1 Shrink Ratio,  
White, .25in [6.4mm] Expanded Inside Diameter, HX-CT[View on TE.com >](#)

Identification &amp; Labeling &gt; Printable Tubing &gt; Continuous Tube, Low Fire Hazard HX-CT

Printable Tubing Type: **Continuous**Printable Tubing Grade: **Low Fire Hazard**Shrink Ratio: **2:1**Primary Product Color: **White**Expanded Inside Diameter (Min): **6.4 mm [ .25 in ]**[All Continuous Tube, Low Fire Hazard HX-CT \(18\)](#)

## Features

### Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Low Fire Hazard

### Body Features

Shrink Ratio	2:1
Primary Product Color	White

### Dimensions

Expanded Inside Diameter (Min)	6.4 mm[.25 in]
Recovered Inside Diameter (Max)	3.2 mm[.125 in]
Compatible Cable Diameter Range	3.2 – 5.12 mm[.125 – .201 in]

### Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

### Packaging Features

Packaging Quantity	50
--------------------	----

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # 1-2186501-1 T3212-SWARE-PRINTER
---	--	---	---



TE Part # CP8122-000  
[T6112DS-PRINTER](#)

## Also in the Series | HX-CT



[Printable Tubing\(27\)](#)

## Customers Also Bought



TE Part #5-1415033-1  
[SR6ZB024](#)



TE Part #DTP04-2P  
[REC, 2P, GRY, N](#)



TE Part #WP-2P  
[WEDGE LOCK, 2P, REC, ORG, DTP](#)



TE Part #926308-3  
[8P UN-MNL AUFN-GEH](#)



TE Part #1-480702-0  
[04P UMNL PLUG HSG NATL](#)



TE Part #1-1623773-1  
[C10 1K0 5% \(LOOSE\)](#)



TE Part #9675813001  
[100G0111-0.50-6](#)

## Documents

### Product Drawings

[HX-CT-50M-6.4-OUT-9](#)

English

### Datasheets & Catalog Pages

[Printable Continuous Tubing](#)

English

## HX-CT, Low Fire Hazard Continuous Heat Shrink Identification Tube

English

---

### Product Specifications

[Product Specification](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English