



- NOTES:
1. Rating: 10A 250VAC CUL;CCC
  2. CONTACT RESISTANCE: 50mΩ Max
  3. INSULATION RESISTANCE: 100MΩ Min, at 500VDC
  4. WITHSTAND VOLTAGE: 2000VAC 0.5mA 1 minute

电话: 0769-82310511-867  
 邮箱: hooya89@hooya.hk

NO.	PART NAME	MATERIAL	Q'TY
8	本体	PA66	1
7	盖子	PA66	1
6	3#端子	C2680 1/2H Ag-plating	2
5	3#PIN	C1100 1/2H Ag-plating	2
4	连接片	C2680 1/2H Tin-plating	1
3	2#PIN	C2680 1/2H Ni-plating	2
2	1#PIN	C2680 1/2H Ni-plating	1
1	1#端子	C2680 1/2H Tin-plating	3

NO	DESCRIPTION	NO	DESCRIPTION	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		DRAWING NO.	REV.
				RANGE	TOLERANCE					MM	NO		
5	→	10	→	X	±0.30	LMC 2019.05.20				SCALE	NO	RT-C14B-C00-13-R	WIF119107
4	→	9	→	X.X	±0.20					MAT'L	***		
3	→	8	→	X.XX	±0.10					MATERIAL NO.			
2	→	7	→	ANGLES	±1°								
1	→	6	→										
LEGIION ELECTRONIC & HARDWARE CO., LTD.													

