

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable



2908520

<https://www.phoenixcontact.com/us/products/2908520>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled, shielded, halogen-free round cable; connection 1: D-SUB socket strip (1x 37-position); connection 2: D-SUB socket strip (1x 37-position); cable length: 6 m



## Commercial data

Item number	2908520
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK2136
Catalog page	Page 593 (C-5-2017)
GTIN	4055626305998
Weight per piece (including packing)	1,259.8 g
Weight per piece (excluding packing)	1,259.8 g
Customs tariff number	85444290
Country of origin	DE

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable



2908520

<https://www.phoenixcontact.com/us/products/2908520>

## Technical data

### Product properties

Product type	System cable
--------------	--------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 2 A (Uncoiled, see derating)

### Cable/line

Cable length	6 m
Number of positions	37
Shielded	yes
Conductor type	Assembled, shielded, halogen-free round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	37x 0.25 mm <sup>2</sup>
Wire diameter incl. insulation	1.2 mm ±0.05 mm
External cable diameter	10.8 mm ±0.5 mm
Outer sheath, material	Halogen-free sheath
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 80 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (at 20 °C)
Smallest bending radius, fixed installation	90 mm
Smallest bending radius, movable installation	170 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	yes
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable)
Resistance to oil	can withstand occasional splashes (raw cable)

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable

2908520

<https://www.phoenixcontact.com/us/products/2908520>



## Connection data

### Connection 1

Connection in acc. with standard	IEC 60807-2
	DIN 41652
Connection method	D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Tightening torque	0.2 Nm
Insertion/withdrawal cycles	> 200
Pitch	2.77 mm

### Connection 2

Connection in acc. with standard	IEC 60807-2
	DIN 41652
Connection method	D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	37
Tightening torque	0.2 Nm
Insertion/withdrawal cycles	> 200
Pitch	2.77 mm

## Notes

General	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
---------	--


# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable



2908520

<https://www.phoenixcontact.com/us/products/2908520>

## Drawings



Maximum permissible current per path in uncoiled state

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable



2908520

<https://www.phoenixcontact.com/us/products/2908520>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908520>

CSA	Approval ID: 70002966	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
		125 V	1 A	-	-

cUL Recognized	Approval ID: FILE E 238705	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
		125 V	1 A	-	-

UL Recognized	Approval ID: FILE E 238705	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
		125 V	1 A	-	-

EAC	Approval ID: RU*-DE.HB*35.B00385
-----	----------------------------------

**cULus Recognized**

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable

2908520

<https://www.phoenixcontact.com/us/products/2908520>



## Classifications

### ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

### ETIM

ETIM 8.0	EC000237
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable

2908520

<https://www.phoenixcontact.com/us/products/2908520>



## Environmental product compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# CABLE-D37SUB/B/B/HF/S/ 6,0M - Cable



2908520

<https://www.phoenixcontact.com/us/products/2908520>

## Accessories

### KME - Cable marker carrier

0807083

<https://www.phoenixcontact.com/us/products/0807083>



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable ties,  
cable diameter: > 5 mm, lettering field size: 20 x 8 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)