





NOTES:

1 TPA&LEVER IN PRE-LOCK STATUS WHEN DELIVERY.

2 TPA&LEVER IN END-LOCK AFTER CONTACT ASSEMBLY.

3.PRODUCT SPEC: 108-101580. APPLICATION SPEC 114-101078


4.MATING PART IS *-2316763-.*.

5.THE APPLICABLE CLIP:2322574-1.

6.THE APPLICATION CONTACT: SEE TABLE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.DANG	25SEP2017	 TE Connectivity	
		CHK E.JIANG	25SEP2017		
		APVD L.YIN	25SEP2017		
		PRODUCT SPEC 108-101580			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 48POS, HYBRID, TAB HSG ASSY, UNSLD	
				-	
				SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-2298631	
				RESTRICTED TO -	
MATERIAL SEE TABLE -material_2-		FINISH -finish_spec_2-		SCALE 1:1	
				SHEET 1 OF 1	
				REV D1	
				CUSTOMER DRAWING	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-18-010243	06SEP2018	A.D	SY.W
	B	ECR-19-002169	25DEC2018	A.D	I.Y
	D	ECR-20-004176	19MAR2020	A.D	N.Z
	D1	ECN-22-169668	16AUG22	W.H	J.Z



CONTACT SIZE(MM)	CABLE SIZE (MM2)	INSULATION DIA(MM)	P/N OF CONTACT	PLATING
0.64	0.22-0.35	1.1-1.4	2297494-1	PRE-TIN
	0.5-0.75	1.4-1.9	2293362-1	PRE-TIN
1.2	0.22-0.35	1.1-1.4	2294463-1	PRE-TIN
	0.5-0.75	1.4-1.9	2294463-2	PRE-TIN
	1.0-1.5	1.9-2.4	2294463-3	PRE-TIN
2.8	0.5-1.0	1.4-2.1	2-964294-1	PRE-TIN
	>1.0-2.5	2.2-3.0	2-964296-1	PRE-TIN
	>2.5-4.0	2.7-3.7	1-968946-1	PRE-TIN
			2-968946-1	PRE-TIN

1	1	RED	PBT-GF15	CPA	4
1	1	BLACK	PBT-GF20	LEVER	3
1	1	NATURE	PBT-GF30	TPA	2
1		YELLOW	PBT-GF20	48POS, HYBRID, TAB HSG, UNSLD, COD B	1
	1	BLACK		48POS, HYBRID, TAB HSG, UNSLD, COD A	
QTY	QTY	COLOR	MATERIAL	DESCRIPTION	NO
45.6	45.6	WEIGHT(g)			
B	A	CODING			
D1	D1	REV			
2298631-2	2298631-1	ASSY P/N			